


19-дюймовый источник питания перем. тока/пост. тока для MicroTCA, с регулированием (PM EMMC), двойной полноразмерный

CATALOG NUMBER

11098-547



Блок питания 600 MTCA — это исключительно эффективный модуль питания (МП) для приложений MicroTCA. Этот блок питания на 600 Вт наиболее эффективен и доступен в полноразмерном формате двойной ширины. Благодаря встроенному контроллеру управления этого МП, он идеально подходит для сложных коммуникационных систем, в которых используются процессоры последнего поколения и увеличено количество модулей АМС. Блок питания MTCA 600 обеспечивает мощность, необходимую для 12 АМС, 2 охлаждающих устройств и 2 контроллеров MicroTca Carrier Hub (MCH).

CERTIFICATIONS



FEATURES

Полноразмерная ширина при удвоенной высоте

PRODUCT ATTRIBUTES

Product Type: Power Supply

Type: 19" Switched-Mode

Works With: MicroTCA Systems

Input Voltage AC: 90 – 264V

Мощность W: 600W

Number of Output Voltages: 2

Voltage 1: 12V

Current 1: 6.8A

Voltage 2: 3.3V

Current 2: 0.18A

Rack Width: 6HP

Глубина мм: 186.65mm

Высота мм: 148.3mm

Net Weight: 1.315kg

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Выходные данные для $T_a = -25 \dots 55^\circ\text{C}$ с принудительным охлаждением 20 куб. фт/мин.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE