


Настольный корпус PropacPRO, неэкранированный, высота 2 U, ширина стойки 42 HP, 266 мм

CATALOG NUMBER

14576-021



Корпус nVent SCHROFF PropacPRO обеспечивает защиту электронных компонентов 19-дюймовых и отдельных электронных узлов. Алюминиевые литые рамы и профильные боковые панели гарантируют надежное решение. Также предлагается широкий ассортимент принадлежностей.

CERTIFICATIONS



FEATURES

Настольный корпус для индивидуальной сборки

Вентиляционные отверстия в нижней крышке

ЭМС-экранирование с возможностью модернизации

Подготовлен для заземления

PRODUCT ATTRIBUTES

Rack Height: 2U

Rack Width: 42HP

Глубина мм: 266mm

Package Quantity: 1

Usable Height: 85.1mm

Usable Width: 219mm

Front Frame Construction: Single Piece

Cooling Option: Нет

Complies With: IEC 60297-3-101

EMC Shielding: No (Retrofittable)

Finish: Passivated; Powder Coated

Высота мм: 111mm

Material: Алюминий

Product Family: PropacPRO

Product Type: Корпус

Protection Rating: IP20

Static Load: 25kg

Type: Case for Individual Electronic Components

Ширина мм: 257mm

Net Weight: 1.66kg

ADDITIONAL PRODUCT DETAILS

Корпус 2 U с боковой панелью со складной ручкой для переноски по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE