


Защитная панель EuropacPRO, Universal



Защитная крышка используется для электромагнитного экранирования или в качестве механической защиты. Крышка может использоваться в случае, если в блочный каркас будут установлены нестандартные платы.

CERTIFICATIONS



FEATURES

Экранирование обеспечивается дополнительными ЭМС-прокладками из нержавеющей стали, между заглушкой и боковой панелью

Для переменного позиционирования горизонтальных реек, например, для печатных плат нестандартных форматов

Степень перфорации 58 %

Возможно использование в комбинации со всеми типами горизонтальных рельсов

SPECIFICATIONS

Material:	Алюминий
Product Type:	Cover Plate
Product Family:	EuropacPRO
Finish:	Passivated
Works With:	Блочный каркас
Type:	Universal

Table 1/1

Catalog Number	Rack Width	Глубина мм	Package Quantity	Package Unit	Quick Ship
----------------	------------	------------	------------------	--------------	------------

24560-031	42HP	175mm	2	Pair	No
24560-032	42HP	235mm	2	Pair	No
24560-033	42HP	295mm	2	Pair	No
24560-041	63HP	175mm	2	Pair	No
24560-042	63HP	235mm	2	Pair	No
24560-043	63HP	295mm	2	Pair	No
24560-051	84HP	175mm	2	Pair	No
24560-052	84HP	235mm	2	Pair	No
24560-053	84HP	295mm	2	Pair	No
24560-054	84HP	355mm	2	Pair	No
24560-055	84HP	415mm	2	Pair	No
24560-056	84HP	475mm	2	Pair	No

ADDITIONAL PRODUCT DETAILS

Кроме того, для закрепления крышки на горизонтальном рельсе требуется 4 контактных лент на каждый блочный каркас.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE