


# Ручка для устройства вставки/извлечения, тип XL, 10 шт.

## CATALOG NUMBER

20817-874



Подходит для усилий вставки и извлечения до 1500 Н (на пару). Надежная фиксация печатных плат с помощью двух винтов. Функция вставки будет поддерживаться при помощи соединительной части, которая будет смонтирована на горизонтальном рельсе.

## CERTIFICATIONS



## FEATURES

Подходит для нагрузок вставки и извлечения до 1500 Н (на пару ручек)

Ручка, материал полиамид, усилена стекловолокном, UL 94V 0

Надежная фиксация платы с двойным винтовым креплением

Микрореле могут быть установлены

Симметричное расположение, идентичная ручка сверху/снизу

PRODUCT ATTRIBUTES

|                                 |
|---------------------------------|
| Product Type: Ручка             |
| Type: Inserter/Extractor        |
| Works With: Передние панели     |
| Handle Type: XL                 |
| Ширина мм: 20.1mm               |
| Material: Zinc Alloy; Polyamide |
| Color: Jet Black                |
| Flammability Rating: UL® 94V-0  |
| Package Quantity: 10            |
| Color Code: RAL 9005            |
| Глубина мм: 42.39mm             |
| Gross Weight: 0.374kg           |
| Высота мм: 73.57mm              |

ADDITIONAL PRODUCT DETAILS

Передние панели и микропереключатель заказываются отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE