


Комплект сменных модулей для РМС с черной ручкой IEL, U-образная лицевая панель, экранированная (текстильная ЭМЗ прокладка), 3 U, 4 HP

CATALOG NUMBER

20836-460



U-образная передняя панель с вырезом для РМС. Возможность экранирования тканевой ЭМС-прокладкой.

FEATURES

В соответствии с требованиями IEEE P1386, мезонинная плата PCI

Для одиночного модуля 69,0 x 76,5 мм или двойного модуля 139,0 x 76,5 мм

Для стандартных мезонинных модулей ввода/вывода, которые подключаются к платам носителя

РМС = мезонинная плата PCI

ПЛИС = программируемая логическая интегральная схема

Передняя панель из U-образного профиля 3 U, 4 HP, с текстильным уплотнителем

ЭМС-экранирование передней панели и крышек для вырезов передней панели

PRODUCT ATTRIBUTES

Rack Height: 3U

Package Quantity: 1

Handle Type: IEL

Mounting: Screw-on Front

Gasket Type: Textile EMC

Front Finish: Anodized

Rear Finish: Conductive

Complies With: Мезионная PMC, IEEE P1386

EMC Shielding: Да

Finish: Anodized; Passivated

Material: Алюминий

Product Type: Передняя панель

Rack Width: 4HP

Type: Front Panel with Handle (PIU)

Net Weight: 0.088kg

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE