

Передняя панель для высокочастотного вставного модуля рамного типа, токопроводящая, 14 HP

CATALOG NUMBER

20838-004



Алюминий, 2,5 мм, передний анодированный, проводящий для ВЧ-кассеты. Без экранирования. Изделие подготовлено для пластиковой передней ручки.

CERTIFICATIONS



FEATURES

алюминий, 2,5 мм, лицевая поверхность анодированная, conductive; trapezium shaped handle, серый, ПФЭ, UL 94 V-1

Передняя панель с ручкой для крепления к высокочастотному сменному блоку

PRODUCT ATTRIBUTES

Rack Width: 14HP

Package Quantity: 1

Аксессуар Тип: Передняя панель

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Нет

Глубина мм (D): 2.5mm

Finish: Anodized; Passivated

Высота мм (H): 128.4mm

Material: Алюминий

Product Type: Передняя панель

Rack Height: 3U


Ширина мм (W): 70.78mm

Gross Weight: 0.072kg

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE