

Источник питания Coolpower, 19 дюймов, перем. / пост. ток, 100 Вт, одинарный



Pluggable 19" Power Supplies with H15 connector for fanless applications.

CERTIFICATIONS



FEATURES

Широкий диапазон входного напряжения 20 ... 72 В пост. тока

Гальваническая развязка между первичной и вторичной цепями

Высокая удельная мощность

Внешний переключатель ВКЛ/ВЫКЛ

SPECIFICATIONS

Table 1/2

Catalog Number	Type	Input Voltage DC	Мощность W	Number of Output Voltages	Voltage 1	Current 1
13103-003	19" DC/DC Converter	20 – 72V	102W	1	12V	8.5A
13103-004	19" DC/DC Converter	20 – 72V	100W	1	15V	6.7A

CatalogNumber	Type	Input Voltage DC	Мощность W	Number of OutputVoltages	Voltage 1	Current 1
13103-002	19" DC/DC Converter	20 – 72V	100W	1	5V	20A

Table 2/2					
Catalog Number	Rack Height	Rack Width	Глубина мм	Package Quantity	Quick Ship
13103-003	3U	6HP	171.93mm	1	No
13103-004	3U	6HP	171.93mm	1	No
13103-002	3U	6HP	171.93mm	1	No

ADDITIONAL PRODUCT DETAILS

Передняя панель заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE