

Varistar CP Rear Panel, крепление на винтах



В шкафах предусмотрены задние панели, хорошо прикрепленные винтами к раме для максимального контакта с прокладкой.

FEATURES

Крепление на винтах, прочная боковая панель для монтажа одним человеком

Задняя панель без комплекта заземления

SPECIFICATIONS

Product Type: Cabinet/Rack Panel

Material: Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Ширина мм	Protection Rating	Package Quantity	Color
21630-384	24U	1200mm	600mm	IP20	1	Black Grey
21630-198	24U	1200mm	600mm	IP55	1	Black Grey
21630-385	24U	1200mm	800mm	IP20	1	Black Grey
21630-204	24U	1200mm	800mm	IP55	1	Black Grey
21630-386	29U	1400mm	600mm	IP20	1	Black Grey
21630-199	29U	1400mm	600mm	IP55	1	Black Grey

CatalogNumber	Rack Height	Высота мм	Ширина мм	Protection Rating	Package Quantity	Color
21630-387	29U	1400mm	800mm	IP20	1	Black Grey
21630-205	29U	1400mm	800mm	IP55	1	Black Grey
21630-388	33U	1600mm	600mm	IP20	1	Black Grey
21630-200	33U	1600mm	600mm	IP55	1	Black Grey
21630-389	33U	1600mm	800mm	IP20	1	Black Grey
21630-206	33U	1600mm	800mm	IP55	1	Black Grey
21630-390	38U	1800mm	600mm	IP20	1	Black Grey
21630-201	38U	1800mm	600mm	IP55	1	Black Grey
21630-391	38U	1800mm	800mm	IP20	1	Black Grey
21630-207	38U	1800mm	800mm	IP55	1	Black Grey
21630-122	42U	2000mm	600mm	IP20	1	Black Grey
21630-202	42U	2000mm	600mm	IP55	1	Black Grey
21630-125	42U	2000mm	800mm	IP20	1	Black Grey
21630-208	42U	2000mm	800mm	IP55	1	Black Grey
21630-123	47U	2200mm	600mm	IP20	1	Black Grey
21630-203	47U	2200mm	600mm	IP55	1	Black Grey
21630-126	47U	2200mm	800mm	IP20	1	Black Grey
21630-209	47U	2200mm	800mm	IP55	1	Black Grey

CatalogNumber	Rack Height	Высота мм	Ширина мм	Protection Rating	Package Quantity	Color
21630-545	24U	1200mm	600mm	IP55	1	
21630-546	24U	1200mm	800mm	IP55	1	
21630-547	29U	1400mm	600mm	IP55	1	
21630-548	29U	1400mm	800mm	IP55	1	
21630-549	33U	1600mm	600mm	IP55	1	
21630-550	33U	1600mm	800mm	IP55	1	
21630-551	38U	1800mm	600mm	IP55	1	
21630-552	38U	1800mm	800mm	IP55	1	
21630-553	42U	2000mm	600mm	IP55	1	
21630-554	42U	2000mm	800mm	IP55	1	
21630-555	47U	2200mm	600mm	IP55	1	
21630-556	47U	2200mm	800mm	IP55	1	
21630-124	52U	2450mm	600mm	IP20	1	Black Grey
21630-127	52U	2450mm	800mm	IP20	1	Black Grey

Table 2/2

Catalog Number	Color Code	Finish	Type	Works With	Quick Ship
21630-384	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-198	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-385	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No

Catalog Number	Color Code	Finish	Type	Works With	Quick Ship
21630-204	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-386	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-199	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-387	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-205	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-388	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-200	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-389	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-206	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-390	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-201	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-391	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-207	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-122	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-202	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-125	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-208	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-123	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No

Catalog Number	Color Code	Finish	Type	Works With	Quick Ship
21630-203	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-126	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-209	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-545		Powder Coated	Rear Panel	Varistar CP	No
21630-546		Powder Coated	Rear Panel	Varistar CP	No
21630-547		Powder Coated	Rear Panel	Varistar CP	No
21630-548		Powder Coated	Rear Panel	Varistar CP	No
21630-549		Powder Coated	Rear Panel	Varistar CP	No
21630-550		Powder Coated	Rear Panel	Varistar CP	No
21630-551		Powder Coated	Rear Panel	Varistar CP	No
21630-552		Powder Coated	Rear Panel	Varistar CP	No
21630-553		Powder Coated	Rear Panel	Varistar CP	No
21630-554		Powder Coated	Rear Panel	Varistar CP	No
21630-555		Powder Coated	Rear Panel	Varistar CP	No
21630-556		Powder Coated	Rear Panel	Varistar CP	No
21630-124	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No
21630-127	RAL 7021	Powder Coated	Rear Panel	Varistar CP	No

ADDITIONAL PRODUCT DETAILS

Комплект заземления можно приобрести отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE