


Монтажная панель Varistar



Монтажная панель Varistar для монтажа электрических компонентов и подузлов с несущей способностью 600 кг. Монтажную панель также можно установить сзади и добавить усиливающий кронштейн для увеличения несущей способности.

CERTIFICATIONS



FEATURES

Для монтажа электрических компонентов и подузлов, включая кабели

Монтажный шаг глубиной 25 мм и высотой 50 мм для монтажа на половину высоты

Допустимая статическая нагрузка до 450 кг (монтаж сзади)

600 кг при полной высоте, монтаж сзади, с дополнительными усиливающими кронштейнами

Укрепляющий кронштейн увеличивает способность к статической нагрузке

600 кг при полной высоте, монтаж сзади, с дополнительными угольниками жесткости

SPECIFICATIONS

Product Type: Монтажная панель
Material: Сталь

Table 1/1					
Catalog Number	Высота мм	Ширина мм	Package Quantity	Finish	Quick Ship
23130-405	1800mm	600mm	1	Zinc Plated	No
23130-414	1200mm	800mm	1	Zinc Plated	No
23130-413	1200mm	600mm	1	Zinc Plated	No
23130-408	2000mm	800mm	1	Zinc Plated	No
23130-406	1800mm	800mm	1	Zinc Plated	No
23130-407	2000mm	600mm	1	Zinc Plated	No

ADDITIONAL PRODUCT DETAILS

Для монтажа на половину высоты требуются заглубляющие распорки.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE