


# Front Panel EMC Textile Shielding Kit, - 40...+85°C, 9 U, 10 шт.

## CATALOG NUMBER

**21102-859**



Текстильные ЭМС-прокладки вставляются в слот с правой стороны U-образных передних панелей. Прокладки приклеиваются к передней панели. Для расширенного диапазона температур до +85°C.

## CERTIFICATIONS



## FEATURES

Текстильный ЭМС-уплотнитель крепится сбоку на передней панели или при необходимости в пазу правого профиля.

Профильное уплотнение наклеивается на контактную поверхность 19-дюймового кронштейна или заднего угла и устанавливает токопроводящее соединение с U-образными передними панелями.

Диапазон температур -40 °C.. +85 °C

## PRODUCT ATTRIBUTES

Rack Height: 9U

Package Quantity: 10

Глубина мм (D): 1.62mm

Высота мм (H): 365.5mm

Material: Thermoplastic Elastomer

Product Family: EuropacPRO; PropacPRO; RatiopacPRO AIR; PropacPRO; Frame Type Plug-In Unit

Product Type: Shielding Kit


Works With: Блочный каркас; Coffrets; Передние панели

Gross Weight: 0.166kg

## ADDITIONAL PRODUCT DETAILS

ЭМС-прокладки (текстильные) необходимы для экранирования передних панелей.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**