


Силовая объединительная плата CPCI Serial, 3 U, 8 HP, 1 слот

CATALOG NUMBER

23098-397



Силовая объединительная плата для режимов применения CompactPCI Serial. Можно подключить до 4 силовых объединительных плат, чтобы увеличить мощность или использовать их в качестве резерва.

CERTIFICATIONS



FEATURES

Силовая объединительная плата для подключаемых источников питания с платой питания FCI

3 U, 8 HP, 1 разъем для источника питания

Отдельные входы для переменного и постоянного тока с разъемами Faston

Разъем для 12 В, 5 В, резервный, сигнальные разъемы Utility, current sharing, power button, последовательная консоль к источнику бесперебойного питания и цифровой ввод-вывод сзади

Дополнительно, можно установить штекер PICMG 2.9 SMBus и дополнительные соединения Powerbug для резервного питания 12 В и 5 В

Географический адрес можно задать с помощью DIP-переключателя

PRODUCT ATTRIBUTES

Product Type: Объединительная плата

Number of Slots: 1

Rack Height: 3U

Backplane Type: CompactPCI Serial

Slot Width: 8HP

Connector Type: 01

Power Connector Type: PwrBlade

Utility Connector Type: MicroMatch, 10-pin

Ширина мм: 39.6mm

Package Quantity: 1

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE