

19-дюймовая передняя панель с отверстиями под ручки

Data Solutions



Оформите фасады и боковые границы устройств с помощью 19-дюймовых передних панелей SCHROFF. 19-дюймовые передние панели SCHROFF имеют дополнительные отверстия для крепления ручки и доступны в диапазоне от 1 U до 6 U.

CERTIFICATIONS



FEATURES

19" передние панели с дополнительными отверстиями для ручек

SPECIFICATIONS

Rack Width:	95HP
Material:	Алюминий
Аксессуар Тип:	Передняя панель
Product Type:	Передняя панель

Table 1/3

Catalog Number	Rack Height	Глубина мм (D)	Handle Type	Finish	Mounting	Package Quantity
30219-161	1U	3mm	Front Handle	Anodized	Screw-on Front	1

CatalogNumber	Rack Height	Глубина мм(D)	Handle Type	Finish	Mounting	Package Quantity
40304-050	1U	3mm	Front Handle	Anodized	Screw-on Front	1
30219-162	2U	3mm	Front Handle	Anodized	Screw-on Front	1
40304-051	2U	3mm	Front Handle	Anodized	Screw-on Front	1
30219-163	3U	3mm	Front Handle	Anodized	Screw-on Front	1
30219-164	4U	3mm	Front Handle	Anodized	Screw-on Front	1
40304-052	3U	3mm	Front Handle	Anodized	Screw-on Front	1
30219-165	5U	3mm	Front Handle	Anodized	Screw-on Front	1
40304-053	4U	3mm	Front Handle	Anodized	Screw-on Front	1
30219-166	6U		Front Handle	Anodized	Screw-on Front	1
40304-054	5U	3mm	Front Handle	Anodized	Screw-on Front	1
40304-055	6U	3mm	Front Handle	Anodized	Screw-on Front	1

Table 2/3						
Catalog Number	Front Finish	Rear Finish	Treated Edges	EMC Shielding	Высота мм (H)	Type
30219-161	Anodized	Anodized	Нет	Нет	43.6mm	19" Front Panel
40304-050	Anodized	Anodized	Да	Нет	43.6mm	19" Front Panel
30219-162	Anodized	Anodized	Нет	Нет	88.1mm	19" Front Panel
40304-051	Anodized	Anodized	Да	Нет	88.1mm	19" Front Panel
30219-163	Anodized	Anodized	Нет	Нет	132.5mm	19" Front Panel

CatalogNumber	Front Finish	Rear Finish	Treated Edges	EMC Shielding	Высота мм (H)	Type
30219-164	Anodized	Anodized	Нет	Нет	177mm	19" Front Panel
40304-052	Anodized	Anodized	Да	Нет	132.5mm	19" Front Panel
30219-165	Anodized	Anodized	Нет	Нет	221.4mm	19" Front Panel
40304-053	Anodized	Anodized	Да	Нет	177mm	19" Front Panel
30219-166	Anodized	Anodized	Нет	Нет	265.9mm	19" Front Panel
40304-054	Anodized	Anodized	Да	Нет	221.4mm	19" Front Panel
40304-055	Anodized	Anodized	Да	Нет	265.9mm	19" Front Panel

Table 3/3

Catalog Number	Ширина мм (W)
30219-161	483mm
40304-050	483mm
30219-162	483mm
40304-051	483mm
30219-163	483mm
30219-164	483mm
40304-052	483mm
30219-165	483mm
40304-053	483mm
30219-166	483mm

