


# Система CompactPCI с источником питания АТХ, высота 3 U, 8 слотов

## CATALOG NUMBER

**24579-031**



Безвентиляторная система CompactPCI 3 U с вертикальным каркасом для печатных плат на восемь плат 3 U и восемь плат RTM. Встроенный источник питания АТХ.

## CERTIFICATIONS



## FEATURES

Система соответствует IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; объединительная плата соответствует PICMG 2.0 верс. 3,0

Система с вертикальным каркасом для печатных плат. Фронтальная плата: 3 U, глубина 160 мм; Задняя панель ввода-вывода: 3 U, глубина 80 мм

Объединительная плата с 8 слотами, 3 U, 32 -разрядная; системный слот справа; Допускается использование ЦП шириной 8 HP

Отвод тепла путем конвекции, воздушный поток снизу вверх

Блок питания АТХ, 300 Вт

Возможность установки DVD-дисков Slim-Line и жесткого диска

PRODUCT ATTRIBUTES

|                                |
|--------------------------------|
| Product Type: System           |
| Number of Slots: 8             |
| Type: 19" Rack Mount           |
| Backplane Type: 3 U CompactPCI |
| Data Transfer: 32-bit PCI Bus  |
| Power per Slot: 10W            |
| Input Voltage AC: 100 – 240V   |
| Rack Height: 3U                |
| Power Supply Type: (1) ATX PSU |
| Power Supply Included: Да      |
| Rear I/O: Да                   |
| Complies With: PICMG 2.0 R3.0  |
| Глубина мм: 275mm              |
| Высота мм: 132.55mm            |
| Net Weight: 8.86kg             |
| Package Quantity: 1            |

ADDITIONAL PRODUCT DETAILS

Модифицированные системы доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause

| North America                                            | Europe                                                   | Asia                                                     | Middle East & India                                      |
|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|----------------------------------------------------------|
| All locations                                            | Straubenhardt, Germany                                   | Shanghai, China                                          | Dubai, United Arab Emirates                              |
| +1.763.422.2661                                          | +49.7082.794.0                                           | +86.21.2412.6943                                         | +971.4.378.1700                                          |
| Chat with us:                                            | Betschdorf, France                                       | Qingdao, China                                           | Bangalore, India                                         |
| <a href="http://nvent.com/schroff">nvent.com/schroff</a> | +33.3.88.90.64.90                                        | +86.532.8771.6101                                        | +91.80.6715.2001                                         |
|                                                          | Warsaw, Poland                                           | Singapore                                                | Istanbul, Turkey                                         |
|                                                          | +48.22.209.98.35                                         | +65.6768.5800                                            | +90.216.250.7374                                         |
|                                                          | Assago, Italy                                            | Shin-Yokohama, Japan                                     | Chat with us:                                            |
|                                                          | +39.02.932.7141                                          | +81.45.476.0271                                          | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |
|                                                          | Chat with us:                                            | Chat with us:                                            |                                                          |
|                                                          | <a href="http://nvent.com/schroff">nvent.com/schroff</a> | <a href="http://nvent.com/schroff">nvent.com/schroff</a> |                                                          |



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE