


# Боковая панель для вставного модуля рамного типа для углового профиля, плата 6 U, 227 мм

## CATALOG NUMBER

**34813-603**



Боковые панели можно вставить в паз углового профиля.

## CERTIFICATIONS



## FEATURES

Боковая панель вставного модуля сконструирована из двух компонентов

Панель вставляется между двумя угловыми профилями

Интегрированный боковой паз в угловом профиле для монтажа одной печатной платы

Боковой паз в угловом профиле для монтажа одной печатной платы

## PRODUCT ATTRIBUTES

Rack Height: 6U

Глубина мм (D): 227mm

Package Quantity: 1

Finish: Passivated

Длина мм (L): 220mm

Material: Алюминий

Product Type: Крышка

Works With: Cassettes


Net Weight: 0.352kg

## ADDITIONAL PRODUCT DETAILS

Угловые профили для конструирования боковой панели заказываются отдельно.

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

## DIAGRAMS



## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**