


Штифт для кодирования напряжения для мезонинных печатных плат PMC

CATALOG NUMBER

60827-026



Штифт для кодирования напряжения для мезонинных печатных плат PMC.

CERTIFICATIONS



FEATURES

Для избежания случайных повреждений при установке мезонинных плат, кодовые штифты крепятся болтами к платам VMEbus, чтобы различать рабочее напряжение 3,3 В и 5 В. Мезонинные платы имеют отверстие, просверленное в соответствующем месте. Таким образом кодовый штифт обеспечивает возможность вставки только мезонинных плат с одинаковым рабочим напряжением. Для европлат двойной ширины требуются 2 штуки.

Штифт для кодирования напряжения для мезонинных печатных плат PMC

PRODUCT ATTRIBUTES

Product Type: Coding/Keying Indicator

Product Family: EuropacPRO; RatiopacPRO; CompacPRO; PropacPRO; Inpac

Type: Coding Peg

Works With: Блочный каркас; Coffrets; CompactPCI Systems; CompactPCI Serial Systems; PXI

Thread Type: Metric

Material: Нержавеющая сталь

Package Quantity: 1

Глубина мм: 13.5mm

Высота мм: 5mm

Длина мм: 13.5mm

Ширина мм: 5mm

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки могут осуществляться в указанных стандартных количествах (SPQ) (SPQ, например, 5 штук, 10 штук, 50 штук и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE