


Наконечник направляющей, 4,4-дюймовая печатная плата, ширина канавки 2 мм, красный

CATALOG NUMBER

64560-057



Пластиковые наконечники для отдельных составных направляющих с пластиковой или алюминиевой средней секцией. Доступные типы: «Стандарт», «Принадлежность» или «4,4-дюймовая печатная плата». Наконечники могут быть дополнительно оснащены зажимом для защиты от электростатического разряда (ESD), который обеспечивает токопроводящий контакт между печатной платой и горизонтальной рейкой. Подходит для RatiopacPRO/-AIR, PropacPRO, CompacPRO и EuropacPRO.

CERTIFICATIONS



FEATURES

Наконечники (полибутилентерефталат) для отдельных составных направляющих со средней секцией из пластика или экструдированного алюминия.

Наконечники направляющих могут крепиться к горизонтальным рейкам (алюминиевый экструдированный профиль) или к панелям толщиной 1,5 мм.

Температура хранения: 0 °C ... +60 °C

Температура хранения от -40 до 130 °C

PRODUCT ATTRIBUTES

Product Type: Rail End Piece
Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; MultipacPRO; Inpac
Type: 4.4" PCB
Works With: Блочный каркас; Coffrets; Chassis
Package Quantity: 1
Package Unit: Pair
Gross Weight: 0.003kg
Material: Polybutylene Terephthalate

ADDITIONAL PRODUCT DETAILS

Поставка исключительно в размере товарной партии. Цена указана за отдельную единицу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE