


# EuropacPRO Adapter for Rear Fixing, DL3 Standard



Адаптер для заднего крепления блочного каркаса в соответствии со стандартом DL3 в шкафу. Он обеспечивает вибростойкость до 25 g.

## CERTIFICATIONS



## FEATURES

Гарантированная вибростойкость до 25 g согласно IEC 61587 DL3

Адаптеры для других моделей шкафа доступны по запросу

Монтаж на заднюю стенку упрочненного блочного каркаса и шкафа Varistar

## SPECIFICATIONS

|                        |                |
|------------------------|----------------|
| <b>Product Type:</b>   | Adapter        |
| <b>Product Family:</b> | EuropacPRO     |
| <b>Works With:</b>     | Блочный каркас |

Table 1/1

| Catalog Number | Rack Height | Package Quantity | Finish                         | Material        | Quick Ship |
|----------------|-------------|------------------|--------------------------------|-----------------|------------|
| 24568-198      | 3U          | 2                | Aluminum-Zinc Plated, Anodized | Сталь, Алюминий | No         |
| 24568-498      | 6U          | 4                | Aluminum-Zinc Plated, Anodized | Сталь, Алюминий | No         |

ADDITIONAL PRODUCT DETAILS

Адаптер не может использоваться вместе с угловым профилем.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE