

Настольный корпус Interscale, с перфорацией



Гибкий настольный корпус с интегрированной защитой от электромагнитных помех и перфорацией сбоку. На основе платформы nVent SCHROFF Interscale и в соответствии с IEC 60297-3-109.

CERTIFICATIONS



FEATURES

Настольный модульный корпус, состоящий из 4 компонентов

Разработано в соответствии с IEC 60297-3-109 (в стадии разработки IEC)

Встроенная защита от ЭМС

Степень защиты от внешних воздействий — до IP 20

Цвет RAL 7016

Модифицированные или изготавливаемые по спецификации заказчика корпуса доступны по запросу

SPECIFICATIONS

Material:	Алюминий; Сталь
Type:	Настольный корпус
Product Family:	Interscale
Protection Rating:	IP20
Color Code:	RAL 7016
Product Type:	Small Form Factor Case

Table 1/2

Catalog Number	Высота мм	Package Quantity	Ширина мм	Глубина мм	Cooling	Color
14825-154	43.7mm	1	221mm	177mm	С перфорацией	Anthracite Grey
14825-155	43.7mm	1	221mm	221mm	С перфорацией	Anthracite Grey
14825-175	43.7mm	1	310mm	221mm	С перфорацией	Anthracite Grey
14825-195	43.7mm	1	399mm	221mm	С перфорацией	Anthracite Grey
14825-197	43.7mm	1	399mm	310mm	С перфорацией	Anthracite Grey
14825-254	88.1mm	1	221mm	177mm	С перфорацией	Anthracite Grey
14825-255	88.1mm	1	221mm	221mm	С перфорацией	Anthracite Grey
14825-275	88.1mm	1	310mm	221mm	С перфорацией	Anthracite Grey
14825-295	88.1mm	1	399mm	221mm	С перфорацией	Anthracite Grey
14825-297	88.1mm	1	399mm	310mm	С перфорацией	Anthracite Grey
14825-375	132.6mm	1	310mm	221mm	С перфорацией	Anthracite Grey
14825-395	132.6mm	1	399mm	221mm	С перфорацией	Anthracite Grey
14825-397	132.6mm	1	399mm	310mm	С перфорацией	Anthracite Grey

Table 2/2

Catalog Number	Finish	Quick Ship
14825-154	Aluminum-Zinc Plated, Powder Coated	No
14825-155	Aluminum-Zinc Plated, Powder Coated	No
14825-175	Aluminum-Zinc Plated, Powder Coated	No

Catalog Number	Finish	Quick Ship
14825-195	Aluminum-Zinc Plated, Powder Coated	No
14825-197	Aluminum-Zinc Plated, Powder Coated	No
14825-254	Aluminum-Zinc Plated, Powder Coated	No
14825-255	Aluminum-Zinc Plated, Powder Coated	No
14825-275	Aluminum-Zinc Plated, Powder Coated	No
14825-295	Aluminum-Zinc Plated, Powder Coated	No
14825-297	Aluminum-Zinc Plated, Powder Coated	No
14825-375	Aluminum-Zinc Plated, Powder Coated	No
14825-395	Aluminum-Zinc Plated, Powder Coated	No
14825-397	Aluminum-Zinc Plated, Powder Coated	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE