

Сетевой кабель



Сетевой кабель nVent SCHROFF обеспечивает практичное, универсальное крепление с помощью различных крепежных приспособлений. Он является универсальным по своей сущности и подходит для различных типов применения, таких как вентиляторы, освещение шкафов и т. д., соединения промышленных ПК, источники бесперебойного питания, системы.

CERTIFICATIONS



FEATURES

Области применения: вентиляторы, освещение шкафа, подключение к промышленному ПК, системы и источники бесперебойного питания

SPECIFICATIONS

Product Type: Cable

Table 1/2

Catalog Number	Input Connector	Output Connector	Длина мм	Package Quantity	Color	Connector Type
60103-131	SCHUKO / UTE	IEC C13	2500mm	1	Серый	Straight
60103-137	BS = British Standard	IEC C13	2500mm	1	Черный	Straight
60103-141	US = US Standard	IEC C13	2500mm	1	Черный	Straight
60197-053	IEC C14	IEC C13	2500mm	1	Черный	Straight

CatalogNumber	InputConnector	Output Connector	Длина мм	Package Quantity	Color	ConnectorType
60110-361	IEC C14	IEC C13	1000mm	1	Черный	Straight
60704-020	SCHUKO / UTE	IEC C13	2500mm	1	Серый	Angled
62150-191	SCHUKO / UTE	IEC C13	2500mm	1	Черный	Straight
60110-360	IEC C14	IEC C13	500mm	1	Черный	Straight

Table 2/2

Catalog Number	Material	Quick Ship
60103-131	PVC	No
60103-137	PVC	No
60103-141	PVC	No
60197-053	PVC	No
60110-361	PVC	No
60704-020	PVC	No
62150-191	PVC	No
60110-360	PVC	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE