


# Набор крепежных деталей Varistar



Монтажный комплект для сборки аксессуаров непосредственно на раме Varistar с наружной или внутренней стороны.

## CERTIFICATIONS



## FEATURES

Монтаж компонентов возможен как изнутри, так и снаружи

Для монтажа 19- монтажных профилей, заглубляющие распорки и другие компоненты на каркасе Varistar

Сборка путем защелкивания кузовной гайки на каркасе или заглубляющей распорке

Комплект требуется в том случае, если задняя панель с быстроразъемным фиксатором установлена над соединительной панелью

## SPECIFICATIONS

|                      |                  |
|----------------------|------------------|
| <b>Product Type:</b> | Монтажные детали |
| <b>Material:</b>     | Сталь            |
| <b>Finish:</b>       | Zinc Plated      |

Table 1/1

| Catalog Number | Package Quantity | Torque | Type  | Quick Ship |
|----------------|------------------|--------|-------|------------|
| 23130-285      | 50               | 5N·m   | Screw | No         |

| Catalog Number | Package Quantity | Torque | Type              | Quick Ship |
|----------------|------------------|--------|-------------------|------------|
| 23130-674      | 50               | 5N·m   | Screw with Washer | No         |
| 23130-141      | 50               |        | Screw with Nuts   | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**