


Панель основания Varistar CP, составная



Составная панель основания устанавливается изнутри.

Защитное заземление, заглушка, щеточный пыльник или фильтерная прокладка заказываются отдельно.

FEATURES

Чтобы закрыть дно шкафа

Составная панель основания открыта в задней части (отверстие сзади глубиной 200 мм, в шкафах глубиной 300 мм заднее отверстие не предусмотрено)

SPECIFICATIONS

Product Type: Cabinet/Rack Base

Material: Сталь

Table 1/2

Catalog Number	Ширина мм	Глубина мм	Package Quantity	Frame	Color	Color Code
21630-616	600mm	600mm	1	Stationary	Black Grey	RAL 7021

CatalogNumber	Ширина мм	Глубина мм	Package Quantity	Frame	Color	Color Code
21630-617	600mm	800mm	1	Stationary	Black Grey	RAL 7021
21630-618	600mm	900mm	1	Stationary	Black Grey	RAL 7021
21630-619	600mm	1000mm	1	Stationary	Black Grey	RAL 7021
21630-620	600mm	1100mm	1	Stationary	Black Grey	RAL 7021
21630-621	600mm	1200mm	1	Stationary	Black Grey	RAL 7021
21630-622	800mm	600mm	1	Stationary	Black Grey	RAL 7021
21630-623	800mm	800mm	1	Stationary	Black Grey	RAL 7021
21630-624	800mm	900mm	1	Stationary	Black Grey	RAL 7021
21630-625	800mm	1000mm	1	Stationary	Black Grey	RAL 7021
21630-626	800mm	1100mm	1	Stationary	Black Grey	RAL 7021
21630-627	800mm	1200mm	1	Stationary	Black Grey	RAL 7021
21630-802	600mm	600mm	1	Mobile	Black Grey	RAL 7021
21630-803	600mm	800mm	1	Mobile	Black Grey	RAL 7021
21630-804	600mm	900mm	1	Mobile	Black Grey	RAL 7021
21630-805	600mm	1000mm	1	Mobile	Black Grey	RAL 7021
21630-806	600mm	1100mm	1	Mobile	Black Grey	RAL 7021
21630-807	600mm	1200mm	1	Mobile	Black Grey	RAL 7021
21630-808	800mm	600mm	1	Mobile	Black Grey	RAL 7021

CatalogNumber	Ширина мм	Глубина мм	Package Quantity	Frame	Color	Color Code
21630-809	800mm	800mm	1	Mobile	Black Grey	RAL 7021
21630-810	800mm	900mm	1	Mobile	Black Grey	RAL 7021
21630-811	800mm	1000mm	1	Mobile	Black Grey	RAL 7021
21630-812	800mm	1100mm	1	Mobile	Black Grey	RAL 7021
21630-813	800mm	1200mm	1	Mobile	Black Grey	RAL 7021

Table 2/2

Catalog Number	Finish	Quick Ship
21630-616	Powder Coated	No
21630-617	Powder Coated	No
21630-618	Powder Coated	No
21630-619	Powder Coated	No
21630-620	Powder Coated	No
21630-621	Powder Coated	No
21630-622	Powder Coated	No
21630-623	Powder Coated	No
21630-624	Powder Coated	No
21630-625	Powder Coated	No
21630-626	Powder Coated	No
21630-627	Powder Coated	No

Catalog Number	Finish	Quick Ship
21630-802	Powder Coated	No
21630-803	Powder Coated	No
21630-804	Powder Coated	No
21630-805	Powder Coated	No
21630-806	Powder Coated	No
21630-807	Powder Coated	No
21630-808	Powder Coated	No
21630-809	Powder Coated	No
21630-810	Powder Coated	No
21630-811	Powder Coated	No
21630-812	Powder Coated	No
21630-813	Powder Coated	No

ADDITIONAL PRODUCT DETAILS

Составная панель основания устанавливается изнутри.

Защитное заземление, заглушка, щеточный пыльник или фильтерная прокладка заказываются отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE