

Outdoor Comline FTTX Cabinet

Data Solutions



Telecom applications require sophisticated electronics in outdoor setups. nVent SCHROFF Outdoor cabinets shield such electronic components from extreme weather, Vandalism and thereby ensuring operational continuity. nVent SCHROFF cabinets can be used as Dslam / Point of Presence / Zone pooling / FTTC / FTTH / MFG cabinets.

CERTIFICATIONS



FEATURES

Height dimensions without plinth (140 mm)

Single wall, lightweight aluminium cabinet

Insulated cabinet

IP 55

SPECIFICATIONS

Material: Алюминий

Table 1/3

Catalog Number	Product Type	Product Family	Rack Height	Высота мм	Ширина мм	Глубина мм
12349-007	Outdoor Cabinet	Comline FTTX	12U	600mm	800mm	600mm

CatalogNumber	Product Type	Product Family	Rack Height	Высота мм	Ширина мм	Глубина мм
12349-006	Outdoor Cabinet	Comline FTTX	25U	1200mm	800mm	600mm
12349-005	Outdoor Cabinet	Comline FTTX	12U	600mm	800mm	600mm
12349-008	Outdoor Cabinet	Comline FTTX	25U	1200mm	800mm	600mm

Table 2/3

Catalog Number	Wall Type	Door Type	Access	Cooling	EMC Shielding	Complies With
12349-007	Single Walled	Single Door	С передней стороны, Back	Изоляционные	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-006	Single Walled	Single Door	С передней стороны, Back	Изоляционные	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-005	Single Walled	Single Door	С передней стороны, Back	Изоляционные	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160
12349-008	Single Walled	Single Door	С передней стороны, Back	Изоляционные	Нет	IEC 61969-1, IEC 61969-2, IEC 60917-1, IEC 60917-2, ETS 300119, IEC 60529, DIN EN 50178, VDE 0160

Table 3/3

Catalog Number	Package Quantity	Finish
----------------	------------------	--------

12349-007	1	Powder Coated
12349-006	1	Powder Coated
12349-005	1	Powder Coated
12349-008	1	Powder Coated

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE