


PFF Parallel Plastic Screw-In Plug for P13/P14 Couplers, Worldwide Design



FEATURES

Designed for use with the P13/P14 coupler families

Designed to keep dirt, water and concrete slurry out of the coupler during the concrete pour

Durable mounting plates allow for easy attachment to forms

Color coded for the appropriate coupler size

SPECIFICATIONS

Design Version: Worldwide (Globally Available Materials)

Table 1/2


Catalog Number	Material	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Height (H)
EL12PFFN	High Density Polyethylene (HDPE), Сталь	12 mm	#4	10M	65 mm	17 mm
EL28PFFN	High Density Polyethylene (HDPE), Сталь	28 mm	#9	30M	95 mm	20 mm
EL40PFFN	High Density Polyethylene (HDPE), Сталь	40 mm			95 mm	20 mm

CatalogNumber	Material	Rebar Size, Metric	Rebar Size, US	Rebar Size, Canada	Diameter (Ø)	Height (H)
EL20PFFN	High Density Polyethylene (HDPE), Сталь	20 mm	#6	20M	75 mm	20 mm
EL36PFFN	High Density Polyethylene (HDPE), Сталь	36 mm	#11	35M	95 mm	20 mm
EL22PFFN	High Density Polyethylene (HDPE), Сталь	22 mm	#7		95 mm	20 mm
EL16PFFN	High Density Polyethylene (HDPE), Сталь	16 mm	#5	15M	65 mm	20 mm
EL32PFFN	High Density Polyethylene (HDPE), Сталь	32 mm	#10		95 mm	20 mm
EL25PFFN	High Density Polyethylene (HDPE), Сталь	25 mm	#8	25M	95 mm	20 mm

Table 2/2

Catalog Number	Color
EL12PFFN	Красный
EL28PFFN	Черный
EL40PFFN	Зеленый
EL20PFFN	Yellow
EL36PFFN	Blue
EL22PFFN	Blue
EL16PFFN	Черный
EL32PFFN	Yellow
EL25PFFN	Красный

DIAGRAMS



WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

+1.800.753.9221
Option 1 – Customer Care
Option 2 – Technical
Support

Europe

Netherlands:
+31 800-0200135
France:
+33 800 901 793

Europe

Germany:
800 1890272
Other Countries:
+31 13 5835404

APAC

Shanghai:
+ 86 21 2412 1618/19
Sydney:
+61 2 9751 8500



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE