


Корпус MiniPac прямоугольной формы, настольный

CATALOG NUMBER

24814-024



Прямоугольный корпус из алюминиевого профиля позволяет пользователю вставлять 4 стандартные печатные платы (высота 100 мм x глубина 160 мм). Платы устанавливаются в пазы в корпусе из алюминиевого профиля. Обе стороны покрываются передними панелями толщиной 2,5 мм.

CERTIFICATIONS



FEATURES

Модули для размещения 4 стандартизированных печатных плат (высота 100 мм, depth 160 мм) or rotated by 90° to accommodate 8 non-standardized PCBs (height 60 mm, глубина 160 мм)

Толщина печатной платы 1,6 мм, шаг пазов 10,16 мм (2 HP)

Длина D = 160 мм, длинная сторона 110,9 мм, короткая сторона 70,3 мм

Настольное исполнение

PRODUCT ATTRIBUTES

Product Type: Small Form Factor Case

Product Family: Minipac

Type: Настольный корпус

Высота мм: 112.3mm

Ширина мм: 71.7mm

Глубина мм: 160.5mm

Material: Алюминий

Color: Черный

Finish: Anodized

Protection Rating: IP40

Cooling: Без перфорации

Shape: Прямоугольный

Package Quantity: 1

Длина мм: 160.5mm

Gross Weight: 0.783kg

ADDITIONAL PRODUCT DETAILS

Другие размеры доступны по запросу:

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE