


Горизонтальная рейка, передняя, тип L-OD, облегченного типа, без кромки, 42 HP

CATALOG NUMBER

34560-042



Combinations of horizontal rails and side panels

	Side panel	Light rail	Standard rail	Heavy rail	Bagged rail
Standard rail	+	+	+	+	+
Light rail	+	+	+	+	+
Heavy rail	+	+	+	+	+
Bagged rail	+	+	+	+	+

Legend: + can be combined, - combination not recommended, * not recommended

Горизонтальная рейка без кромки позволяет использовать такие устройства, как передняя панель 6 U, для блочного каркаса, разделенного на 2 x 3 U.

CERTIFICATIONS



FEATURES

Для установки позади передней панели на всю ширину

< 28 HP без маркировки

Без кромки (L-OD)

Алюминиевый экструдированный профиль, анодированная поверхность, электропроводящая контактная поверхность

PRODUCT ATTRIBUTES

Rack Width: 42HP

Package Quantity: 1

Finish: Anodized

Длина мм: 218.44mm

Material: Алюминий

Product Family: EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO

Product Type: Горизонтальный рельс

Type: Light, OD

Works With: Блочный каркас; Coffrets

Net Weight: 0.067kg

ADDITIONAL PRODUCT DETAILS

Обратите внимание, что поставки доступны в указанных стандартных товарных партиях (товарная партия, например, 5 шт., 10 шт., 50 шт. и т. д.). Другие объемы заказов (например, 2 шт.) могут округляться вверх до следующего возможного размера стандартной товарной партии.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE