


Монтажный комплект для откидной ручки RatiopacPro



Данный монтажный комплект должен использоваться в случае, если необходимо установить откидную ручку. Стандартные боковые крышки следует заменить.

CERTIFICATIONS



FEATURES

Алюминиевая боковая панель с порошковым покрытием RAL 9006, адаптер и монтажный материал.

SPECIFICATIONS

Product Type:	Монтажные детали
Works With:	Coffrets
Product Family:	RatiopacPRO; RatiopacPRO AIR
Type:	Tip-Up Handle Kit

Table 1/2

Catalog Number	Rack Height	Rack Width	Глубина мм	Package Quantity	Finish	Material
24571-352	3U	42HP	255mm	2	Powder Coated	Алюминий
24571-353	3U	42HP	315mm	2	Powder Coated	Алюминий

CatalogNumber	Rack Height	Rack Width	Глубина мм	Package Quantity	Finish	Material
24571-354	3U	42HP	375mm	2	Powder Coated	Алюминий
24571-355	3U	42HP	435mm	2	Powder Coated	Алюминий
24571-356	3U	42HP	495mm	2	Powder Coated	Алюминий
24571-359	4U	42HP	255mm	2	Powder Coated	Алюминий
24571-360	4U	42HP	315mm	2	Powder Coated	Алюминий
24571-361	4U	42HP	375mm	2	Powder Coated	Алюминий
24571-362	4U	42HP	435mm	2	Powder Coated	Алюминий
24571-363	4U	42HP	495mm	2	Powder Coated	Алюминий

Table 2/2	
Catalog Number	Quick Ship
24571-352	No
24571-353	No
24571-354	No
24571-355	No
24571-356	No
24571-359	No
24571-360	No
24571-361	No
24571-362	No

Catalog Number	Quick Ship
24571-363	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE