

T-stycke för ren kanal på 90 grader



Clean Tray 90-Degree Tees are used for right-angle installations where two 90-degree transitions are required. The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown.

DESIGN

Clean Tray 90-Degree Tees are used for right-angle installations where two 90-degree transitions are required

The Clean Tray stainless steel system is designed to protect rated cabling in applications that require frequent washdown

SPECIFIKATIONER

Yta: Borstad #3

Material: Rostfritt stål 304

Table 1/1

Katalognummer	Typ	Höjd	Bredd	Tjocklek	Snabbleverans
CT22TFCSS	T-stycke	51mm	51mm	1.27mm	Nej
CT33TFCSS	T-stycke	76mm	76mm	1.27mm	Nej
CT33TICSS	T-stycke	76mm	76mm	1.27mm	Nej
CT33TOCSS	T-stycke	76mm	76mm	1.27mm	Nej
CT44PTFCSS	T-stycke	102mm	102mm	1.27mm	Nej
CT44TFCSS	T-stycke	102mm	102mm	1.27mm	Nej
CT44TICSS	T-stycke	102mm	102mm	1.27mm	Nej
CT44TOCSS	T-stycke	102mm	102mm	1.27mm	Nej
CT46TFCSS	T-stycke	102mm	152mm	1.27mm	Nej
CT46TICSS	T-stycke	102mm	152mm	1.27mm	Nej
CT46TOCSS	T-stycke	102mm	152mm	1.27mm	Nej
CT66TFCSS	T-stycke	152mm	152mm	1.27mm	Nej
CT66TICSS	T-stycke	152mm	152mm	1.27mm	Nej
CT66TOCSS	T-stycke	152mm	152mm	1.27mm	Nej
CTS33PTFCSS	T-stycke	76mm	76mm	1.27mm	Nej
CTS33TFCSS	T-stycke	76mm	76mm	1.27mm	Nej
CTS44PTFCSS	T-stycke	102mm	102mm	1.27mm	Nej

Katalognummer	Typ	Höjd	Bredd	Tjocklek	Snabbleverans
CTS44TFCSS	T-stycke	102mm	102mm	1.27mm	Nej
CTS46PTFCSS	T-stycke	102mm	152mm	1.27mm	Nej
CTS46TFCSS	T-stycke	102mm	152mm	1.27mm	Nej
CTS66PTFCSS	T-stycke	152mm	152mm	1.27mm	Nej
CTS66TFCSS	T-stycke	152mm	152mm	1.27mm	Nej
CT22PTFCSS	T-stycke	51mm	51mm	1.27mm	Nej
CT22TOCSS	T-stycke	51mm	51mm	1.27mm	Nej
CT33PTFCSS	T-stycke	76mm	76mm	1.27mm	Nej
CT46PTFCSS	T-stycke	102mm	152mm	1.27mm	Nej
CT66PTFCSS	T-stycke	152mm	152mm	1.27mm	Nej

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE