

Hylla för luftströmbrytare (ACB) för strömdistribution, MSCC



The galvanised steel shelf, MSCC, covers a partial depth of an enclosure and is ideal for equipment requiring strong fixation, such as heavy air circuit breakers. It leaves the rear of the enclosure accessible for easy installation and wiring.

DESIGN

Beskrivning: Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette. The shelf has ventilation slots to allow air circulation in the section. It can be mounted only if we have internal side panels MSPSxx06 in both sides. Adjustable height position in steps of 25mm. It can not be used with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections.

Material: 2 mm galvanised steel.

Leverans: 1 piece with mounting material.

Monteringsdelar ingår

In order to mount the shelf, internal side panels (MSPS), are required

Shelf to mount air circuit-breakers, fixed or withdrawable version and MCCB's version in cassette

The shelf has ventilation slots to allow air circulation in the section

It can be mounted only if we have internal side panels MSPSxx06 in both sides

Adjustable height position in steps of 25mm

d with the front covers system, if it is necessary to increase the internal segregation or limit the access, we recommend to use top and bottom shelf and 3 partial doors to separate the incoming, ACB and outgoing subsections it can not be use

Includes mounting hardware

SPECIFIKATIONER

Tjocklek: 2mm
Material: Mjukt stål
Slutför: Pläterade

Table 1/1

Katalognummer	E-nummer	Höjd	Bredd	Djup	Monteringsplattans bredd	Max. monteringsdjup
MSCC1006	2504759	78mm	1000mm	600mm	904mm	283mm
MSCC0606	2504757	78mm	600mm	600mm	504mm	283mm
MSCC0806	2504758	78mm	800mm	600mm	704mm	283mm

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Vårt starka utbud av varumärken:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE