


EuropacPRO Cover Plate for Bolting to Side Panel

Power Utilities



A cover plate is used for electromagnetic shielding or as mechanical protection. The cover can be screwed onto the side panel.

CERTIFICATIONS



FEATURES

For variable positioning of horizontal rails e.g. for PCBs with standard formats

Perforation degree 58%

Suitable for use with all horizontal rails

SPECIFICATIONS

Table 1/2

Catalog Number	Rack Width	Глубина мм	Package Quantity	Product Family	Product Type	Type
24560-064	42 HP	175 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-065	42 HP	235 mm	1	EuropacPRO	Cover Plate	С перфорацией

CatalogNumber	Rack Width	Глубина мм	Package Quantity	Product Family	Product Type	Type
24560-066	42 HP	295 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-071	63 HP	175 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-072	63 HP	235 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-073	63 HP	295 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-078	84 HP	175 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-079	84 HP	235 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-080	84 HP	295 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-081	84 HP	355 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-082	84 HP	415 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-083	84 HP	475 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-061	42 HP	275 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-062	63 HP	275 mm	1	EuropacPRO	Cover Plate	С перфорацией
24560-063	84 HP	275 mm	1	EuropacPRO	Cover Plate	С перфорацией
24579-090	42 HP	277.75 mm	1	EuropacPRO	Cover Plate	С перфорацией
24579-092	84 HP	277.75 mm	1	EuropacPRO	Cover Plate	С перфорацией

Table 2/2

Catalog Number	Works With	Package Unit	Torque
24560-064	Блочный каркас	Pair	2.1 N·m
24560-065	Блочный каркас	Pair	2.1 N·m

Catalog Number	Works With	Package Unit	Torque
24560-066	Блочный каркас	Pair	2.1 N·m
24560-071	Блочный каркас	Pair	2.1 N·m
24560-072	Блочный каркас	Pair	2.1 N·m
24560-073	Блочный каркас	Pair	2.1 N·m
24560-078	Блочный каркас	Pair	2.1 N·m
24560-079	Блочный каркас	Pair	2.1 N·m
24560-080	Блочный каркас	Pair	2.1 N·m
24560-081	Блочный каркас	Pair	2.1 N·m
24560-082	Блочный каркас	Pair	2.1 N·m
24560-083	Блочный каркас	Pair	2.1 N·m
24560-061	Блочный каркас	Pair	
24560-062	Блочный каркас	Pair	
24560-063	Блочный каркас	Pair	
24579-090	Блочный каркас	Pair	2.1 N·m
24579-092	Блочный каркас	Pair	2.1 N·m

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE