


# Novastar Rear Panel Full Height

## Power Utilities



Steel Rear Panel for aluminum extruded enclosure is connected with 2 twist-locking catches (Torx T30, with 1/4 turn).

## CERTIFICATIONS



## FEATURES

Incl. grounding

2 twist-locking catches (Torx T30, with 1/4 turn)

St, 1 mm

## SPECIFICATIONS

Table 1/1

| Catalog Number | Height | Width | Color | Color Code | Product Type | Type |
|----------------|--------|-------|-------|------------|--------------|------|
|----------------|--------|-------|-------|------------|--------------|------|

|           |         |        |            |          |                    |            |
|-----------|---------|--------|------------|----------|--------------------|------------|
| 25230-370 | 323 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 26230-370 | 323 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 25230-371 | 422 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 26230-371 | 422 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 25230-147 | 1345 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-372 | 555 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-373 | 733 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-374 | 911 mm  | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-375 | 1133 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-376 | 1534 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-377 | 1711 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-378 | 1933 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 25230-379 | 2111 mm | 553 mm | Black Grey | RAL 7021 | Cabinet/Rack Panel | Rear Panel |
| 26230-147 | 1345 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-372 | 555 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-373 | 733 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-374 | 911 mm  | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-375 | 1133 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-376 | 1534 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |

|           |         |        |            |          |                    |            |
|-----------|---------|--------|------------|----------|--------------------|------------|
| 26230-377 | 1711 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-378 | 1933 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |
| 26230-379 | 2111 mm | 553 mm | Light Grey | RAL 7035 | Cabinet/Rack Panel | Rear Panel |

## ADDITIONAL PRODUCT DETAILS

Optional locking with key (2233x).

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.



Our powerful portfolio of brands:

CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE