

EuropacPRO 19" Subrack Kit for Backplane, Slide Rail, Retrofit Shielding

Energiföretag



Non-shielded subrack for backplane, subrack can be assembled on slide rails to support the subrack inside a cabinet.

CERTIFIERING



FUNKTIONER

Subrack with side panel type F ("Flexible"), 19" bracket is depth-adjustable

Subrack can be used with slide rails

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 11 kg

Threaded insert, insulation strip pre-fitted

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Djup	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-132	3 U	235 mm	1	Backplane	160 mm, 220 mm	Rostfritt stål

Katalognummer	Rack Height	Djup	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24553-133	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rostfritt stål
24553-134	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål
24553-432	6 U	235 mm	1	Backplane	160 mm, 220 mm	Rostfritt stål
24553-433	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Rostfritt stål
24553-434	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm, 340 mm	Rostfritt stål

Table 2/3

Katalognummer	Handle Included	Montering	Uppfyller kraven enligt	EMC Shielding	Product Type	Rack Width
24553-132	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24553-133	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24553-134	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24553-432	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24553-433	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP
24553-434	Nej	Rack	IEC 60297-3-103	Nej	Subrack/Chassis	84 HP

Table 3/3

Katalognummer	Statisk belastning
24553-132	11 kgf
24553-133	11 kgf
24553-134	11 kgf
24553-432	11 kgf

Katalognummer	Statisk belastning
24553-433	11 kgf
24553-434	11 kgf

ADDITIONAL PRODUCT DETAILS

Alternative product for older EuropacLab and Europac subrack series.

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE