


Front Panel EMC Textile Shielding Kit, -40 up to +85°C

Energiföretag



The textile EMC gaskets are inserted into a slot on the right hand side of the U-shaped front panels. The gaskets are glued to the front panel. For an expanded temperature range up to +85°C.

CERTIFIERING



FUNKTIONER

Textile EMC gasket is affixed laterally on the front panel or in the groove of the right-hand profile as appropriate.

Profile seal is bonded onto the contact surface of the 19" bracket or of the rear angle and sets up the conductive connection to the U-shaped front panels

Temperature range -40 °C ... +85 °C

SPECIFIKATIONER

Table 1/1

Katalognummer	Rack Height	Package Quantity	Product Family	Product Type	Fungerar med
---------------	-------------	------------------	----------------	--------------	--------------

21102-857	2 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-853	3 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-854	3 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-858	4 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-978	5 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-855	6 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-856	6 U	100	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels
21102-859	9 U	10	EuropacPRO, PropacPRO, RatiopacPRO AIR, PropacPRO, Frame Type Plug-In Unit	Shielding Kit	Subracks, Cases, Front Panels

ADDITIONAL PRODUCT DETAILS

EMC gaskets (textile) are required for shielding the front panels.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE