

Front Panel, Unshielded, With Fastener Pin

Energiföretag



Front panel with GND/earthing connection. The grounding can be done with a cable which fits to the fastener pin on the rear side of the panel.

CERTIFIERING



FUNKTIONER

Enable grounding of the front area (protection class 1)

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Width	Package Quantity	Montering	Front Finish	Rear Finish	Treated Edges
20119-159	7 HP	1	Screw-on Front	Anodized	Conductive	Nej
20119-160	14 HP	1	Screw-on Front	Anodized	Conductive	Nej
20119-161	21 HP	1	Screw-on Front	Anodized	Conductive	Nej
20119-162	28 HP	1	Screw-on Front	Anodized	Conductive	Nej

Katalognummer	Rack Width	Package Quantity	Montering	Front Finish	Rear Finish	Treated Edges
20119-163	42 HP	1	Screw-on Front	Anodized	Anodized	Nej

Table 2/3

Katalognummer	Uppfyller kraven enligt	EMC Shielding	Höjd	Material	Product Type	Rack Height
20119-159	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium	Front Panel	3 U
20119-160	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium	Front Panel	3 U
20119-161	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium	Front Panel	3 U
20119-162	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium	Front Panel	3 U
20119-163	IEC 60297-3-101, IEEE 1101.1/10	Nej	128.4 mm	Aluminium	Front Panel	3 U

Table 3/3

Katalognummer	Typ	Bredd
20119-159	Front Panel without Handle	35.2 mm
20119-160	Front Panel without Handle	70.8 mm
20119-161	Front Panel without Handle	106.3 mm
20119-162	Front Panel without Handle	141.9 mm
20119-163	Front Panel without Handle	213 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

Delivery is in standard pack multiples. Pricing is per individual item.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE