

Guide Rail Accessories for Heavy PCBs, Extra Strong

Energiföretag



This reinforced guide rail for heavy PCBs of the type accessory, forms a reliable interface between the subrack mechanics and the sub-assemblies. The guide rails can additionally be bolted to the horizontal

CERTIFIERING



FUNKTIONER

For especially heavy PCBs, plug-in units or frame type plug-in units

Mounting, for bolting to type H (heavy) and type R (rugged) horizontal rails only

Aluminium profile

SPECIFIKATIONER

Table 1/2

Katalognummer	Board Depth	Groove Width	Färg	Material	Product Family	Product Type
---------------	-------------	--------------	------	----------	----------------	--------------

34562-884	340 mm	2	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-885	400 mm	2	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-881	160 mm	2	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-883	280 mm	2	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34562-882	220 mm	2	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-881	160 mm	2.5	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail

34564-882	220 mm	2.5	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-883	280 mm	2.5	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-884	340 mm	2.5	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail
34564-885	400 mm	2.5	Silver	Aluminium	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail

Table 2/2

Katalognummer	Typ	Fungerar med
34562-884	Extra kraftig	Subracks, Cases, Chassis
34562-885	Extra kraftig	Subracks, Cases, Chassis
34562-881	Extra kraftig	Subracks, Cases, Chassis
34562-883	Extra kraftig	Subracks, Cases, Chassis
34562-882	Extra kraftig	Subracks, Cases, Chassis

Katalognummer	Typ	Fungerar med
34564-881	Extra kraftig	Subracks, Cases, Chassis
34564-882	Extra kraftig	Subracks, Cases, Chassis
34564-883	Extra kraftig	Subracks, Cases, Chassis
34564-884	Extra kraftig	Subracks, Cases, Chassis
34564-885	Extra kraftig	Subracks, Cases, Chassis

ADDITIONAL PRODUCT DETAILS

Delivery is exclusively in standard pack quantity.

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE