

Guide Rail With Coding, preassembled ESD Clip for CompactPCI/ VME64x, PC

Energiföretag

FUNKTIONER

NEW generation with coding type plastic guide rails for reliable retention of PCBs or plug-in units

Significantly increased stability, due to an optimized design and high quality material (PC)

Improved fire safety properties, fulfills EN 45545-2 requirement sets R22, R23 and R24 with HL3

"Halogen-Free", according to IEC 61249-2-21

Can be clipped into horizontal rails (Al extrusion) or into 1.5 mm thick plates

Can be bolted to the horizontal rails Type H and R for higher shock and vibration requirements

ESD clip for an conductive contact between PCB and horizontal rail preassembled

Storage temperature: from -40 °C ... 130 °C

SPECIFIKATIONER

Table 1/2

Katalognummer	Färg	Package Quantity	Board Depth	Groove Width	Uppfyller kraven enligt	Material
24568-847	Röd	10	160 mm	2	EN 45545-2	Polykarbonat
24568-848	Grå	10	160 mm	2	EN 45545-2	Polykarbonat
24568-850	Röd	10	160 mm	2	EN 45545-2	Polykarbonat
24568-851	Grå	10	160 mm	2	EN 45545-2	Polykarbonat
24568-853	Röd	10	70 mm	2	EN 45545-2	Polykarbonat

Katalognummer	Färg	Package Quantity	Board Depth	Groove Width	Uppfyller kraven enligt	Material
24568-854	Grå	10	70 mm	2	EN 45545-2	Polykarbonat
24568-855	Röd	10	70 mm	2	EN 45545-2	Polykarbonat
24568-856	Grå	10	70 mm	2	EN 45545-2	Polykarbonat

Table 2/2				
Katalognummer	Product Family	Product Type	Typ	Fungerar med
24568-847	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-848	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-850	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-851	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-853	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-854	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

Katalognummer	Product Family	Product Type	Typ	Fungerar med
24568-855	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems
24568-856	EuropacPRO, RatiopacPRO, RatiopacPRO AIR, CompacPRO, PropacPRO, MultipacPRO, Inpac	Guide Rail	With Coding and preassembled ESD Clips	Subracks, Cases, 19" Chassis, Systems

ADDITIONAL PRODUCT DETAILS

Please take into consideration that deliveries may be carried out in the stated SPQs (SPQ, e.g. 5 pieces, 10 pieces, 50 pieces, etc.). Differing order quantities (e.g. 2 pieces) may be changed to the next possible delivery quantity = Standard Pack Quantity.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE