

Interscale 19" Rack Mount Chassis, Non-Perforated

Energiföretag

Flexible 19" Chassis with integrated EMC protection. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.



CERTIFIERING



FUNKTIONER

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases available upon request

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Djup	Package Quantity	Usable Width	Montering	Uppfyller kraven enligt
---------------	-------------	------	------------------	--------------	-----------	-------------------------

14821-105	1 U	221.45 mm	1	443.7 mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-107	1 U	310.35 mm	1	443.7 mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-205	2 U	221.45 mm	1	443.7 mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-207	2 U	310.35 mm	1	443.7 mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-305	3 U	221.45 mm	1	443.7 mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-307	3 U	310.35 mm	1	443.7 mm	Rack	IEC 60297-3-100, IEC 60297-3-109

Table 2/2

Katalognummer	EMC Shielding	Product Family	Product Type	Typ
14821-105	Ja	Interscale	Small Form Factor Case	Solid
14821-107	Ja	Interscale	Small Form Factor Case	Solid
14821-205	Ja	Interscale	Small Form Factor Case	Solid
14821-207	Ja	Interscale	Small Form Factor Case	Solid
14821-305	Ja	Interscale	Small Form Factor Case	Solid
14821-307	Ja	Interscale	Small Form Factor Case	Solid

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE