

Novastar Cabinet Without Door and Rear Panel

Energiföretag



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTIFIERING



FUNKTIONER

Static load-carrying capacity up to 400 kg (see specification table)

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Colors: RAL 7021 or color combination RAL 7021/ RAL 7035

Bolted, die-cast frame with Al extrusions

Without door and rear panel

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Frame Color	Höjd	Frame Color Code	Cladding Material	Bredd
---------------	-------------	-------------	------	------------------	-------------------	-------

15230-001	9 U	Black Grey	456 mm	RAL 7021	Stål	553 mm
16230-001	9 U	Black Grey	456 mm	RAL 7021	Stål	553 mm
15230-002	12 U	Black Grey	589 mm	RAL 7021	Stål	553 mm
15230-003	12 U	Black Grey	589 mm	RAL 7021	Stål	553 mm
16230-002	12 U	Black Grey	589 mm	RAL 7021	Stål	553 mm
16230-003	12 U	Black Grey	589 mm	RAL 7021	Stål	553 mm
15230-004	16 U	Black Grey	767 mm	RAL 7021	Stål	553 mm
15230-005	16 U	Black Grey	767 mm	RAL 7021	Stål	553 mm
16230-004	16 U	Black Grey	767 mm	RAL 7021	Stål	553 mm
16230-005	16 U	Black Grey	767 mm	RAL 7021	Stål	553 mm
15230-006	20 U	Black Grey	945 mm	RAL 7021	Stål	553 mm
15230-007	20 U	Black Grey	945 mm	RAL 7021	Stål	553 mm
15230-008	20 U	Black Grey	945 mm	RAL 7021	Stål	553 mm
16230-006	20 U	Black Grey	945 mm	RAL 7021	Stål	553 mm
16230-007	20 U	Black Grey	945 mm	RAL 7021	Stål	553 mm
16230-008	20 U	Black Grey	945 mm	RAL 7021	Stål	553 mm
15230-009	25 U	Black Grey	1167 mm	RAL 7021	Stål	553 mm
15230-010	25 U	Black Grey	1167 mm	RAL 7021	Stål	553 mm
16230-009	25 U	Black Grey	1167 mm	RAL 7021	Stål	553 mm

16230-010	25 U	Black Grey	1167 mm	RAL 7021	Stål	553 mm
15230-011	34 U	Black Grey	1567 mm	RAL 7021	Stål	553 mm
15230-012	34 U	Black Grey	1567 mm	RAL 7021	Stål	553 mm
16230-011	34 U	Black Grey	1567 mm	RAL 7021	Stål	553 mm
16230-012	34 U	Black Grey	1567 mm	RAL 7021	Stål	553 mm
15230-013	38 U	Black Grey	1745 mm	RAL 7021	Stål	553 mm
15230-014	38 U	Black Grey	1745 mm	RAL 7021	Stål	553 mm
16230-013	38 U	Black Grey	1745 mm	RAL 7021	Stål	553 mm
16230-014	38 U	Black Grey	1745 mm	RAL 7021	Stål	553 mm
15230-015	43 U	Black Grey	1967 mm	RAL 7021	Stål	553 mm
15230-016	43 U	Black Grey	1967 mm	RAL 7021	Stål	553 mm
16230-015	43 U	Black Grey	1967 mm	RAL 7021	Stål	553 mm
16230-016	43 U	Black Grey	1967 mm	RAL 7021	Stål	553 mm
15230-017	47 U	Black Grey	2145 mm	RAL 7021	Stål	553 mm
15230-018	47 U	Black Grey	2145 mm	RAL 7021	Stål	553 mm
16230-017	47 U	Black Grey	2145 mm	RAL 7021	Stål	553 mm
16230-018	47 U	Black Grey	2145 mm	RAL 7021	Stål	553 mm

Table 2/3

Katalognummer	Cladding Color	Djup	Statisk belastning	Cladding Color Code	Uppfyller kraven enligt	Frame Material
---------------	----------------	------	--------------------	---------------------	-------------------------	----------------

15230-001	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-001	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-002	Black Grey	500 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-003	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-002	Light Grey	500 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-003	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-004	Black Grey	500 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-005	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-004	Light Grey	500 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-005	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-006	Black Grey	500 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-007	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-008	Black Grey	800 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-006	Light Grey	500 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-007	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-008	Light Grey	800 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-009	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-010	Black Grey	800 mm	200 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-009	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium

16230-010	Light Grey	800 mm	200 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-011	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-012	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-011	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-012	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-013	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-014	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-013	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-014	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-015	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-016	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-015	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-016	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium
15230-017	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
15230-018	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60297-3-100	Aluminium
16230-017	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium
16230-018	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60297-3-100	Aluminium

Table 3/3

Katalognummer	Product Type
15230-001	Cabinet

Katalognummer	Product Type
16230-001	Cabinet
15230-002	Cabinet
15230-003	Cabinet
16230-002	Cabinet
16230-003	Cabinet
15230-004	Cabinet
15230-005	Cabinet
16230-004	Cabinet
16230-005	Cabinet
15230-006	Cabinet
15230-007	Cabinet
15230-008	Cabinet
16230-006	Cabinet
16230-007	Cabinet
16230-008	Cabinet
15230-009	Cabinet
15230-010	Cabinet
16230-009	Cabinet

Katalognummer	Product Type
16230-010	Cabinet
15230-011	Cabinet
15230-012	Cabinet
16230-011	Cabinet
16230-012	Cabinet
15230-013	Cabinet
15230-014	Cabinet
16230-013	Cabinet
16230-014	Cabinet
15230-015	Cabinet
15230-016	Cabinet
16230-015	Cabinet
16230-016	Cabinet
15230-017	Cabinet
15230-018	Cabinet
16230-017	Cabinet
16230-018	Cabinet

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation,

missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE