


Novastar Side Panel for Heavy-Duty

Energiföretag



Steel Side Panels for Heavy-Duty aluminum frame with quick fastener for easy mounting and installation. Schroff delivers cladding parts with grounding cable installed and tested.

CERTIFIERING



FUNKTIONER

With quick-release fastener, includes grounding

St. 1mm

SPECIFIKATIONER

Table 1/2

Katalognummer	Rack Height	Höjd	Djup	Färg	Color Code	Product Type
25230-067	12 U	531 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

Katalognummer	Rack Height	Höjd	Djup	Färg	Color Code	Product Type
25230-068	12 U	531 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-222	12 U	531 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-272	12 U	531 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-067	12 U	531 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-068	12 U	531 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-222	12 U	531 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-272	12 U	531 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-322	12 U	531 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-069	16 U	709 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-080	16 U	709 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-223	16 U	709 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-273	16 U	709 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-323	16 U	709 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-069	16 U	709 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-080	16 U	709 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-223	16 U	709 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-273	16 U	709 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-323	16 U	709 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Katalognummer	Rack Height	Höjd	Djup	Färg	Color Code	Product Type
25230-103	20 U	887 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-104	20 U	887 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-224	20 U	945 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-274	20 U	945 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-324	20 U	945 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-103	20 U	887 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-104	20 U	887 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-224	20 U	945 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-274	20 U	945 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-324	20 U	945 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-105	25 U	1109 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-106	25 U	1109 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-225	25 U	1167 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-275	25 U	1167 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-325	25 U	1167 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-105	25 U	1109 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-106	25 U	1109 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-225	25 U	1167 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Katalognummer	Rack Height	Höjd	Djup	Färg	Color Code	Product Type
26230-275	25 U	1167 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-325	25 U	1167 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-107	34 U	1509 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-108	34 U	1509 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-226	34 U	1567 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-276	34 U	1567 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-326	34 U	1567 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-107	34 U	1509 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-108	34 U	1509 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-226	34 U	1567 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-276	34 U	1567 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-326	34 U	1567 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-109	38 U	1687 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-110	38 U	1687 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-227	38 U	1745 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-277	38 U	1745 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-327	38 U	1745 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-109	38 U	1687 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel

Katalognummer	Rack Height	Höjd	Djup	Färg	Color Code	Product Type
26230-110	38 U	1687 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-227	38 U	1745 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-277	38 U	1745 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-327	38 U	1745 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-111	43 U	1909 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-112	43 U	1909 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-228	43 U	1967 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-278	43 U	1967 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-328	43 U	1967 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-111	43 U	1909 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-112	43 U	1909 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-228	43 U	1967 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-278	43 U	1967 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-328	43 U	1967 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-040	47 U	2087 mm	900 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-041	47 U	2087 mm	1000 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-229	47 U	2145 mm	500 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
25230-279	47 U	2145 mm	600 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

Katalognummer	Rack Height	Höjd	Djup	Färg	Color Code	Product Type
25230-329	47 U	2145 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel
26230-040	47 U	2087 mm	900 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-041	47 U	2087 mm	1000 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-229	47 U	2145 mm	500 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-279	47 U	2145 mm	600 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
26230-329	47 U	2145 mm	800 mm	Light Grey	RAL 7035	Cabinet/Rack Panel
25230-322		531 mm	800 mm	Black Grey	RAL 7021	Cabinet/Rack Panel

Table 2/2

Katalognummer	Typ	Bredd
25230-067	Side Panel	
25230-068	Side Panel	
25230-222	Side Panel	
25230-272	Side Panel	
26230-067	Side Panel	
26230-068	Side Panel	
26230-222	Side Panel	
26230-272	Side Panel	
26230-322	Side Panel	
25230-069	Side Panel	

Katalognummer	Typ	Bredd
25230-080	Side Panel	
25230-223	Side Panel	553 mm
25230-273	Side Panel	553 mm
25230-323	Side Panel	553 mm
26230-069	Side Panel	
26230-080	Side Panel	
26230-223	Side Panel	553 mm
26230-273	Side Panel	553 mm
26230-323	Side Panel	553 mm
25230-103	Side Panel	
25230-104	Side Panel	
25230-224	Side Panel	553 mm
25230-274	Side Panel	553 mm
25230-324	Side Panel	553 mm
26230-103	Side Panel	
26230-104	Side Panel	
26230-224	Side Panel	553 mm
26230-274	Side Panel	553 mm

Katalognummer	Typ	Bredd
26230-324	Side Panel	553 mm
25230-105	Side Panel	
25230-106	Side Panel	
25230-225	Side Panel	553 mm
25230-275	Side Panel	553 mm
25230-325	Side Panel	553 mm
26230-105	Side Panel	
26230-106	Side Panel	
26230-225	Side Panel	553 mm
26230-275	Side Panel	553 mm
26230-325	Side Panel	553 mm
25230-107	Side Panel	
25230-108	Side Panel	
25230-226	Side Panel	553 mm
25230-276	Side Panel	553 mm
25230-326	Side Panel	553 mm
26230-107	Side Panel	
26230-108	Side Panel	

Katalognummer	Typ	Bredd
26230-226	Side Panel	553 mm
26230-276	Side Panel	553 mm
26230-326	Side Panel	553 mm
25230-109	Side Panel	
25230-110	Side Panel	
25230-227	Side Panel	553 mm
25230-277	Side Panel	553 mm
25230-327	Side Panel	553 mm
26230-109	Side Panel	
26230-110	Side Panel	
26230-227	Side Panel	553 mm
26230-277	Side Panel	553 mm
26230-327	Side Panel	553 mm
25230-111	Side Panel	
25230-112	Side Panel	
25230-228	Side Panel	553 mm
25230-278	Side Panel	553 mm
25230-328	Side Panel	553 mm

Katalognummer	Typ	Bredd
26230-111	Side Panel	
26230-112	Side Panel	
26230-228	Side Panel	553 mm
26230-278	Side Panel	553 mm
26230-328	Side Panel	553 mm
25230-040	Side Panel	
25230-041	Side Panel	
25230-229	Side Panel	553 mm
25230-279	Side Panel	553 mm
25230-329	Side Panel	553 mm
26230-040	Side Panel	
26230-041	Side Panel	
26230-229	Side Panel	553 mm
26230-279	Side Panel	553 mm
26230-329	Side Panel	553 mm
25230-322	Side Panel	

ADDITIONAL PRODUCT DETAILS

Optionally the quarter-turn fastener can be fitted with a side panel lock.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE