

Varistar CP Cabinet Frame, Seismic

Energiföretag

Welded, steel enclosure engineered specifically to protect equipment in areas with seismic activity and satisfy Bellcore Zore 4 requirements.

FUNKTIONER

St, 1.5 mm, zinc-plated, finish: powder-coated

Earthquake resistance to Bellcore Zone 4

Welded seismic frame with strengthening brackets, RAL 7021

Dynamic load-carrying capacity 250 kg to IEC 61587-2

SPECIFIKATIONER

Table 1/3

Katalognummer	Rack Height	Höjd	Bredd	Djup	Shock and Vibration Tolerance	Färg
20630-358	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-359	33 U	1600 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-360	33 U	1600 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-361	33 U	1600 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-362	38 U	1800 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-363	38 U	1800 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-364	38 U	1800 mm	800 mm	600 mm	5 g (force)	Black Grey

Katalognummer	Rack Height	Höjd	Bredd	Djup	Shock and Vibration Tolerance	Färg
20630-365	38 U	1800 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-366	42 U	2000 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-367	42 U	2000 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-368	42 U	2000 mm	600 mm	1000 mm	5 g (force)	Black Grey
20630-369	42 U	2000 mm	600 mm	1200 mm	5 g (force)	Black Grey
20630-370	42 U	2000 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-371	42 U	2000 mm	800 mm	800 mm	5 g (force)	Black Grey
20630-372	42 U	2000 mm	800 mm	1000 mm	5 g (force)	Black Grey
20630-373	42 U	2000 mm	800 mm	1200 mm	5 g (force)	Black Grey
20630-374	47 U	2200 mm	600 mm	600 mm	5 g (force)	Black Grey
20630-375	47 U	2200 mm	600 mm	800 mm	5 g (force)	Black Grey
20630-376	47 U	2200 mm	800 mm	600 mm	5 g (force)	Black Grey
20630-377	47 U	2200 mm	800 mm	800 mm	5 g (force)	Black Grey

Table 2/3

Katalognummer	Color Code	Uppfyller kraven enligt	Frame Material	Material	Product Type	Statisk belastning
20630-358	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-359	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-360	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf

Katalognummer	Color Code	Uppfyller kraven enligt	Frame Material	Material	Product Type	Statisk belastning
20630-361	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-362	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-363	RAL 7021	IEC 61587-1, IEC 61587-2	Stål		Cabinet/Rack Frame	1600 kgf
20630-364	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-365	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-366	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-367	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-368	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-369	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-370	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-371	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-372	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-373	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-374	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-375	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-376	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf
20630-377	RAL 7021	IEC 61587-1, IEC 61587-2	Stål	Stål	Cabinet/Rack Frame	1600 kgf

Table 3/3

Katalognummer	Typ	Fungerar med
---------------	-----	--------------

20630-358	Seismisk	Varistar CP
20630-359	Seismisk	Varistar CP
20630-360	Seismisk	Varistar CP
20630-361	Seismisk	Varistar CP
20630-362	Seismisk	Varistar CP
20630-363	Seismisk	Varistar CP
20630-364	Seismisk	Varistar CP
20630-365	Seismisk	Varistar CP
20630-366	Seismisk	Varistar CP
20630-367	Seismisk	Varistar CP
20630-368	Seismisk	Varistar CP
20630-369	Seismisk	Varistar CP
20630-370	Seismisk	Varistar CP
20630-371	Seismisk	Varistar CP
20630-372	Seismisk	Varistar CP
20630-373	Seismisk	Varistar CP
20630-374	Seismisk	Varistar CP
20630-375	Seismisk	Varistar CP
20630-376	Seismisk	Varistar CP

20630-377	Seismisk	Varistar CP
-----------	----------	-------------

ADDITIONAL PRODUCT DETAILS

Please order attachments and components separately.

VARNING

nVent produkter ska installeras och användas endast så som anges i nVents bruksanvisning och utbildningsmaterial. Bruksanvisningar är tillgängliga på www.nvent.com och från din nVent kundtjänstrepresentant. Felaktig installation, missbruk, felapplicering eller annan brist i att helt följa nVents instruktioner och varningar kan orsaka att produkten brister, egendomsskador, allvarliga kroppsskador och dödsfall och/eller ogiltigförklara din garanti.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE