


Объединительная плата VPX, высота 3 U, 7 слотов, ВКР3-CEN07-15.2.3-4

CATALOG NUMBER

23001-814



Объединительная плата nVent SCHROFF VPX обеспечивает превосходную целостность сигнала для самых высоких скоростей передачи данных.

CERTIFICATIONS



FEATURES

В соответствии с: Базовый стандарт VITA 46.0 VPX; VITA 46.3 Serial RapidIO на VPX; VITA 46.4 PCI Express на коммутационном разъеме VPX; VITA 46.7 Ethernet на коммутационном разъеме VPX; Управление системой VITA 46.11 для VPX

DIP-переключатель для настройки системного слота

Разъемы JTAG

Блокируемые вспомогательные разъемы и сенсорные разъемы

Резьбовые клеммы питания M4, макс. 22 А на слот для каждого значения напряжения

PRODUCT ATTRIBUTES

Product Type: Объединительная плата

Number of Slots: 7

Rack Height: 3U

Backplane Type: VPX, VITA 65

Slot Width: 5HP

Connector Type: MultiGig

Power Connector Type: Powerstuds M4

Utility Connector Type: Microfit, 8-pin

Ширина мм: 186.46mm

Net Weight: 0.675kg

Package Quantity: 1

ADDITIONAL PRODUCT DETAILS

Другие варианты объединительных плат VPX и специальных конструкций объединительной платы VPX доступны по запросу.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE