


WBT Performance Cable Tray Polymer Insert



The nVent CADDY WBT Performance Cable Tray Polymer Insert utilizes a flame-retardant polymer to envelop the entire tray-providing bottom, side and cover protection. Available options include a flat bottom or a prescored version to the tray depth for coverage of the bottom and sides.

功能

Standard black finish for use with divider posts

Polymer insert rolls into the tray bottom

Multiple color options to coordinate with cable tray selection

技术参数

完成: N/A

材料: 聚合物

Table 1/1


物料号	颜色	高度 (H)	宽度 (W)	长度 (L)	单位重量	包含侧板
WBTFORM04B A	黑色		92.2 mm	3048mm	0.02 kg	否

物料号	颜色	高度 (H)	宽度 (W)	长度 (L)	单位重量	包含侧板
WBTFORM06B A	黑色		143 mm	3048mm	0.03 kg	否
WBTFORM08B A	黑色		193.8 mm	3048mm	0.04 kg	否
WBTFORM2X4 BA	黑色	50.8 mm	92.2 mm	3048mm	0.04 kg	是
WBTFORM2X6 BA	黑色	50.8 mm	143 mm	3048mm	0.05 kg	是
WBTFORM12B A	黑色		295.4 mm	3048mm	0.06 kg	否
WBTFORM2X8 BA	黑色	50.8 mm	193.8 mm	3048mm	0.06 kg	是
WBTFORM4X4 BA	黑色	101.6 mm	92.2 mm	3048mm	0.06 kg	是
WBTFORM4X6 BA	黑色	101.6 mm	143 mm	3048mm	0.07 kg	是
WBTFORM16B A	黑色		397 mm	3048mm	0.08 kg	否
WBTFORM2X12 BA	黑色	50.8 mm	295.4 mm	3048mm	0.08 kg	是
WBTFORM4X8 BA	黑色	101.6 mm	193.8 mm	3048mm	0.08 kg	是
WBTFORM18B A	黑色		447.8 mm	3048mm	0.09 kg	否

物料号	颜色	高度 (H)	宽度 (W)	长度 (L)	单位重量	包含侧板
WBTFORM20B A	黑色		498.6 mm	3048mm	0.1 kg	否
WBTFORM2X16 BA	黑色	50.8 mm	397 mm	3048mm	0.1 kg	是
WBTFORM4X12 BA	黑色	101.6 mm	295.4 mm	3048mm	0.1 kg	是
WBTFORM6X8 BA	黑色	152.4 mm	193.8 mm	3048mm	0.1 kg	是
WBTFORM2X18 BA	黑色	50.8 mm	447.8 mm	3048mm	0.11 kg	是
WBTFORM24B A	黑色		600.2 mm	3048mm	0.12 kg	否
WBTFORM2X20 BA	黑色	50.8 mm	498.6 mm	3048mm	0.12 kg	是
WBTFORM4X16 BA	黑色	101.6 mm	397 mm	3048mm	0.12 kg	是
WBTFORM6X12 BA	黑色	152.4 mm	295.4 mm	3048mm	0.12 kg	是
WBTFORM4X18 BA	黑色	101.6 mm	447.8 mm	3048mm	0.13 kg	是
WBTFORM2X24 BA	黑色	50.8 mm	600.2 mm	3048mm	0.14 kg	是
WBTFORM4X20 BA	黑色	101.6 mm	498.6 mm	3048mm	0.14 kg	是

物料号	颜色	高度 (H)	宽度 (W)	长度 (L)	单位重量	包含侧板
WBTFORM6X16 BA	黑色	152.4 mm	397 mm	3048mm	0.14 kg	是
WBTFORM4X24 BA	黑色	101.6 mm	600.2 mm	3048mm	0.16 kg	是
WBTFORM6X18 BA	黑色	152.4 mm	447.8 mm	3048mm	0.16 kg	是
WBTFORM6X20 BA	黑色	152.4 mm	498.6 mm	3048mm	0.18 kg	是
WBTFORM6X24 BA	黑色	152.4 mm	600.2 mm	3048mm	0.18 kg	是

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE

