


水管接地夹钳



The nVent ERICO Water Pipe Ground Clamp provides a highly reliable method for grounding copper conductors to metallic water pipes or ground rods, essential for electrical safety in residential, commercial, and industrial systems. Constructed from high-strength silicone bronze, this clamp ensures excellent durability, corrosion resistance, and secure, long-lasting electrical connections. Its robust design makes it a trusted component for creating effective grounding paths in accordance with applicable electrical codes and standards.

认证



功能

高强度硅胶青铜

用于连接铜导体与金属水管或接地棒

Designed for effectively connecting copper conductors to metallic water pipes or ground rods

Ensures a secure and low-resistance path for grounding applications

Suitable for a range of conductor and pipe sizes


技术参数

Table 1/1

物料号	订货号	材料	管道标称尺寸 (Ø)	管道实际尺寸 (Ø)	认证
CWP1JJ	710262	硅青铜	1/2" - 1"	12.7 - 25.4 mm	
ZWP1J	710268	锌合金	1/2" - 1"	12.7 - 25.4 mm	cUL, UL

物料号	订货号	材料	管道标称尺寸 (Ø)	管道实际尺寸 (Ø)	认证
CWP1JU	710266	硅青铜	1/2" - 1"	12.7 - 25.4 mm	CSA, UL, cUL
CWP2JU	710267	硅青铜	1 1/4" - 2"	31.8 - 50.8 mm	cUL, CSA, UL
CWP4J	710264	硅青铜	2 1/2" - 4"	63.5 - 101.6 mm	CSA, UL, cUL
CWP6J	710265	硅青铜	4 1/2" - 6"	108.0 - 152.4 mm	CSA

图



警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

⚠ WARNING: This product can expose you to chemicals including lead, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov.

北美

+1.800.753.9221
，按 1 转客户服务
，按 2 转技术支持

欧洲

荷兰：
+31 800-0200135
法国：
+33 800 901 793

欧洲

德国：
800 1890272
其他国家/地区：
+31 13 5835404

亚太地区

上海：
+ 86 21 2412 1618/19
悉尼：
+61 2 9751 8500



我们强大的品牌组合：

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE