

панель электропитания, BS



Компактная модульная конструкция панели электропитания с множеством функциональных элементов. Распределительный блок питания с алюминиевым шасси размером 1 U x 1 U легко интегрируется в шкаф с розетками BS.

CERTIFICATIONS



FEATURES

Возможен горизонтальный и вертикальный монтаж

При установке панель электропитания можно развернуть в любую сторону (с шагом 90°)

В соответствии с британским стандартом BS 1363

Установочная высота 1 U

230 В., 13 А

Кабель питания 2 м с разъемом BS (встроенный предохранитель)

Розетки британского стандарта

SPECIFICATIONS

Material:	Алюминий; Polyamide
Color:	Серый
Product Type:	Панели электропитания

Table 1/2

Catalog Number	Socket Type	Socket Quantity	Switched Outlets	Voltage AC	Package Quantity	Глубина мм
----------------	-------------	-----------------	------------------	------------	------------------	------------

60110-245	BS	6	Да	230V	1	44mm
60110-243	BS	7	Нет	230V	1	44mm
60110-244	BS	10	Нет	230V	1	44mm

Table 2/2			
Catalog Number	Finish	Длина мм	Quick Ship
60110-245	Anodized	438.5mm	No
60110-243	Anodized	438.5mm	No
60110-244	Anodized	947.5mm	No

ADDITIONAL PRODUCT DETAILS

Кронштейн для вертикального монтажа заказывается отдельно.

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE