


# Стальная двойная дверь Varistar CP, Перфорированная, 3-точечное запирание



Перфорированная двойная стальная дверь Varistar CP с 3-точечным запиранием и 2 дверными петлями для областей применения с классом защиты IP 20.

## FEATURES

Двустворчатая перфорированная стальная дверь с 3-точечным запиранием для обеспечения класса защиты IP

Поворотная ручка с кнопкой, ключ

Угол открытия 180°

Стандартный монтаж, замок на правой двери

Возможность дооснащения профильным DIN-полуцилиндром

## SPECIFICATIONS

**Locking Type:** 3-Point Locking

**Product Type:** Cabinet Door

**Protection Rating:** IP20

**Material:** Сталь

Table 1/2

| Catalog Number | Rack Height | Высота мм | Ширина мм | Package Quantity | Color      | Color Code |
|----------------|-------------|-----------|-----------|------------------|------------|------------|
| 21630-448      | 24U         | 1200mm    | 600mm     | 1                | Black Grey | RAL 7021   |
| 21630-449      | 24U         | 1200mm    | 800mm     | 1                | Black Grey | RAL 7021   |
| 21630-450      | 29U         | 1400mm    | 600mm     | 1                | Black Grey | RAL 7021   |

| CatalogNumber | Rack Height | Высота мм | Ширина мм | Package Quantity | Color      | Color Code |
|---------------|-------------|-----------|-----------|------------------|------------|------------|
| 21630-451     | 29U         | 1400mm    | 800mm     | 1                | Black Grey | RAL 7021   |
| 21630-452     | 33U         | 1600mm    | 600mm     | 1                | Black Grey | RAL 7021   |
| 21630-453     | 33U         | 1600mm    | 800mm     | 1                | Black Grey | RAL 7021   |
| 21630-454     | 38U         | 1800mm    | 600mm     | 1                | Black Grey | RAL 7021   |
| 21630-455     | 38U         | 1800mm    | 800mm     | 1                | Black Grey | RAL 7021   |
| 21630-020     | 42U         | 2000mm    | 600mm     | 1                | Black Grey | RAL 7021   |
| 21630-027     | 42U         | 2000mm    | 800mm     | 1                | Black Grey | RAL 7021   |
| 21630-021     | 47U         | 2200mm    | 600mm     | 1                | Black Grey | RAL 7021   |
| 21630-028     | 47U         | 2200mm    | 800mm     | 1                | Black Grey | RAL 7021   |
| 21630-022     | 52U         | 2450mm    | 600mm     | 1                | Black Grey | RAL 7021   |
| 21630-029     | 52U         | 2450mm    | 800mm     | 1                | Black Grey | RAL 7021   |

Table 2/2

| Catalog Number | Complies With            | Finish        | Type                          | Works With  | Quick Ship |
|----------------|--------------------------|---------------|-------------------------------|-------------|------------|
| 21630-448      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-449      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-450      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-451      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-452      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-453      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |

| Catalog Number | Complies With            | Finish        | Type                          | Works With  | Quick Ship |
|----------------|--------------------------|---------------|-------------------------------|-------------|------------|
| 21630-454      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-455      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-020      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-027      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-021      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-028      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-022      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |
| 21630-029      | IEC 61587-1, IEC 61587-3 | Powder Coated | Steel Double Door, Perforated | Varistar CP | No         |

## ADDITIONAL PRODUCT DETAILS

Профильный DIN-полуцилиндр для поворотной ручки заказывается отдельно

Комплект заземления можно приобрести отдельно.

Please purchase the grounding kit separately.

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**