

Varistar CP Server Cabinet With Castors



Сварная стальная рама для высоких динамических нагрузок. Подходит для интеграции 19-дюймового ИТ-оборудования.

FEATURES

Предварительно сконфигурирован, готовый к использованию шкаф

Высокая динамическая нагрузка 1000 кг с интегрированными поворотными роликами, допустимая статическая нагрузка до 1600 кг

Степень защиты IP 20

Возможна установка различного ИТ-оборудования

Встроенные панели для управления воздушными потоками для охлаждения спереди назад

Легко интегрируется в систему изолированного коридора

SPECIFICATIONS

Static Load:	1600kg
Product Type:	Rack
Cladding Color Code:	RAL 7021
Frame Material:	Сталь

Table 1/2

Catalog Number	Rack Height	Высота мм	Cladding Material	Ширина мм	Cladding Color	Глубина мм
10630-022	42U	2000mm	Сталь	800mm	Black Grey	1200mm

CatalogNumber	Rack Height	Высота мм	Cladding Material	Ширина мм	Cladding Color	Глубина мм
10630-021	42U	2000mm	Сталь	600mm	Black Grey	1200mm

Table 2/2

Catalog Number	Package Quantity	Dynamic Load	Finish	Material	Type	Quick Ship
10630-022	1	1000kgf	Powder Coated	Сталь	Mobile	No
10630-021	1	1000kgf	Powder Coated	Сталь	Mobile	No

WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at www.nvent.com and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE