


# Кронштейн адаптера для рамы Varistar Deco



Кронштейны адаптера помогают при креплении направляющих рельсов и полок для рамного шкафа Varistar открытого типа с рамой Deco.

## CERTIFICATIONS



## FEATURES

Для крепления направляющих рельсов и полок в шкафу VARISTAR Deco

## SPECIFICATIONS

|                      |         |
|----------------------|---------|
| <b>Product Type:</b> | Bracket |
| <b>Material:</b>     | Сталь   |

Table 1/2

| Catalog Number | Rack Height | Высота мм | Package Quantity | Color      | Color Code | Finish        |
|----------------|-------------|-----------|------------------|------------|------------|---------------|
| 23130-220      | 24U         | 1200mm    | 2                | Black Grey | RAL 7021   | Powder Coated |
| 23130-221      | 29U         | 1400mm    | 2                | Black Grey | RAL 7021   | Powder Coated |
| 23130-222      | 33U         | 1600mm    | 2                | Black Grey | RAL 7021   | Powder Coated |
| 23130-223      | 38U         | 1800mm    | 2                | Black Grey | RAL 7021   | Powder Coated |
| 23130-224      | 42U         | 2000mm    | 2                | Black Grey | RAL 7021   | Powder Coated |
| 23130-225      | 47U         | 2200mm    | 2                | Black Grey | RAL 7021   | Powder Coated |
| 23130-230      | 24U         | 1200mm    | 2                | Light Grey | RAL 7035   | Powder Coated |
| 23130-231      | 29U         | 1400mm    | 2                | Light Grey | RAL 7035   | Powder Coated |
| 23130-232      | 33U         | 1600mm    | 2                | Light Grey | RAL 7035   | Powder Coated |
| 23130-233      | 38U         | 1800mm    | 2                | Light Grey | RAL 7035   | Powder Coated |
| 23130-234      | 42U         | 2000mm    | 2                | Light Grey | RAL 7035   | Powder Coated |
| 23130-235      | 47U         | 2200mm    | 2                | Light Grey | RAL 7035   | Powder Coated |

Table 2/2

| Catalog Number | Type               | Ширина мм | Works With            | Quick Ship |
|----------------|--------------------|-----------|-----------------------|------------|
| 23130-220      | Bracket            | 600mm     | Varistar, Varistar CP | No         |
| 23130-221      | Deco Frame Bracket | 600mm     | Cabinet, Varistar CP  | No         |
| 23130-222      | Deco Frame Bracket | 600mm     | Cabinet, Varistar CP  | No         |
| 23130-223      | Deco Frame Bracket | 600mm     | Cabinet, Varistar CP  | No         |

| Catalog Number | Type               | Ширина мм | Works With           | Quick Ship |
|----------------|--------------------|-----------|----------------------|------------|
| 23130-224      | Deco Frame Bracket | 600mm     | Cabinet, Varistar CP | No         |
| 23130-225      | Deco Frame Bracket | 600mm     | Cabinet, Varistar CP | No         |
| 23130-230      | Deco Frame Bracket | 600mm     | Cabinet              | No         |
| 23130-231      | Deco Frame Bracket | 600mm     | Cabinet              | No         |
| 23130-232      | Deco Frame Bracket | 600mm     | Cabinet              | No         |
| 23130-233      | Deco Frame Bracket | 600mm     | Cabinet              | No         |
| 23130-234      | Deco Frame Bracket | 600mm     | Cabinet              | No         |
| 23130-235      | Deco Frame Bracket | 600mm     | Cabinet              | No         |

## WARNING

nVent products shall be installed and used only as indicated in nVent's product instruction sheets and training materials. Instruction sheets are available at [www.nvent.com](http://www.nvent.com) and from your nVent customer service representative. Improper installation, misuse, misapplication or other failure to completely follow nVent's instructions and warnings may cause product malfunction, property damage, serious bodily injury and death and/or void your warranty.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](http://nvent.com/schroff)



Our powerful portfolio of brands:

**CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE**