

带拉杆把手的 AMC 填充模块



这款 AdvancedMC 填充模块由不带 LED 的不锈钢前面板组成，左侧和底部配有 EMC 垫片。填充模块通过塑料头部装置的卡扣式结构固定在机箱插件导轨中。此模块可用于覆盖空插槽，以确保 EMC 屏蔽效果并关闭前面板，将泄漏的空气密封在机箱中。这些填充模块可用于 AdvancedMC 承载装置和 MicroTCA 插槽。不需要锁杆。

认证



功能

符合 AMC.0 R2.0 技术参数

屏蔽式填充模块可用于封闭未使用的插槽

拉杆把手，用于拔出子组件

可选的空气挡板（可调节气流）可用于引导机箱气流

技术参数

产品系列: AdvancedMC

类型: 填充模块

产品类型: 系统模块

Table 1/1

物料号	设计特征	材料	完成	包装数量	快速发货
20849-249	中尺寸	铝	钝化	1	No

物料号	设计特征	材料	完成	包装数量	快速发货
20849-022	紧凑型	不锈钢		1	No
20849-250	全尺寸	铝	钝化	1	No
20849-106	中尺寸	不锈钢		1	No
20849-248	中尺寸	铝	钝化	1	No
20849-025	全尺寸	不锈钢		1	No
20849-251	全尺寸	铝	钝化	1	No
20849-024	全尺寸	不锈钢		1	No
20849-107	中尺寸	不锈钢		1	No

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客户经理索取。 更多信息，请访问 www.nvent.com 或联系您的客户经理。

North America	Europe	Asia	Middle East & India
All locations +1.763.422.2661 Chat with us: nvent.com/schroff	Straubenhardt, Germany +49.7082.794.0 Betschdorf, France +33.3.88.90.64.90 Warsaw, Poland +48.22.209.98.35 Assago, Italy +39.02.932.7141 Chat with us: nvent.com/schroff	Shanghai, China +86.21.2412.6943 Qingdao, China +86.532.8771.6101 Singapore +65.6768.5800 Shin-Yokohama, Japan +81.45.476.0271 Chat with us: nvent.com/schroff	Dubai, United Arab Emirates +971.4.378.1700 Bangalore, India +91.80.6715.2001 Istanbul, Turkey +90.216.250.7374 Chat with us: nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE