


Varistar CP 底板, 单件

底板结构坚固，可覆盖机柜底板。



功能

底板坚固，覆盖在机柜的底座上

从外部装配

技术参数

产品类型: 机柜/机架底座

材料: 钢

Table 1/2

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
21630-629	600mm	600mm	1			热浸镀锌
21630-630	600mm	800mm	1			热浸镀锌
21630-635	800mm	600mm	1			热浸镀锌
21630-636	800mm	800mm	1			热浸镀锌
21630-628	600mm	300mm	1			热浸镀锌

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
21630-631	600mm	900mm	1			热浸镀锌
21630-632	600mm	1000mm	1			热浸镀锌
21630-637	800mm	900mm	1			热浸镀锌
21630-638	800mm	1000mm	1			热浸镀锌
21630-320	600mm	300mm	1	暗灰色	RAL 7021	粉末涂层
21630-322	600mm	600mm	1	暗灰色	RAL 7021	粉末涂层
21630-323	600mm	800mm	1	暗灰色	RAL 7021	粉末涂层
21630-324	600mm	900mm	1	暗灰色	RAL 7021	粉末涂层
21630-325	600mm	1000mm	1	暗灰色	RAL 7021	粉末涂层
21630-326	600mm	1100mm	1	暗灰色	RAL 7021	粉末涂层
21630-327	600mm	1200mm	1	暗灰色	RAL 7021	粉末涂层
21630-330	800mm	600mm	1	暗灰色	RAL 7021	粉末涂层
21630-331	800mm	800mm	1	暗灰色	RAL 7021	粉末涂层
21630-332	800mm	900mm	1	暗灰色	RAL 7021	粉末涂层
21630-333	800mm	1000mm	1	暗灰色	RAL 7021	粉末涂层
21630-334	800mm	1100mm	1	暗灰色	RAL 7021	粉末涂层
21630-335	800mm	1200mm	1	暗灰色	RAL 7021	粉末涂层

物料号	宽度	深度	包装数量	颜色	颜色代码	完成
21630-633	600mm	1100mm	1			热浸镀锌
21630-634	600mm	1200mm	1			热浸镀锌
21630-639	800mm	1100mm	1			热浸镀锌
21630-640	800mm	1200mm	1			热浸镀锌

Table 2/2	
物料号	快速发货
21630-629	No
21630-630	No
21630-635	No
21630-636	No
21630-628	No
21630-631	No
21630-632	No
21630-637	No
21630-638	No
21630-320	No
21630-322	No

物料号	快速发货
21630-323	No
21630-324	No
21630-325	No
21630-326	No
21630-327	No
21630-330	No
21630-331	No
21630-332	No
21630-333	No
21630-334	No
21630-335	No
21630-633	No
21630-634	No
21630-639	No
21630-640	No

其他产品详情

本底板用于不需要底部电缆入口的应用。

请单独购买接地套件。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE