

Varistar CP Base/Plinth Side

侧边饰件可以安装到 Varistar CP 基座/底座



功能

基座/底座侧板, 平板式

技术参数

产品类型: 机柜/机架底座

材料: 钢

Table 1/2

物料号	高度	深度	包装数量	颜色	颜色代码	完成
24630-083	100mm	300mm	1	暗灰色	RAL 7021	粉末涂层
24630-084	200mm	300mm	1	暗灰色	RAL 7021	粉末涂层
24630-077	100mm	600mm	1	暗灰色	RAL 7021	粉末涂层
24630-080	200mm	600mm	1	暗灰色	RAL 7021	粉末涂层
24630-078	100mm	800mm	1	暗灰色	RAL 7021	粉末涂层
24630-081	200mm	800mm	1	暗灰色	RAL 7021	粉末涂层

物料号	高度	深度	包装数量	颜色	颜色代码	完成
24630-079	100mm	900mm	1	暗灰色	RAL 7021	粉末涂层
24630-082	200mm	900mm	1	暗灰色	RAL 7021	粉末涂层
24630-038	100mm	1000mm	1	暗灰色	RAL 7021	粉末涂层
24630-041	200mm	1000mm	1	暗灰色	RAL 7021	粉末涂层
24630-039	100mm	1100mm	1	暗灰色	RAL 7021	粉末涂层
24630-042	200mm	1100mm	1	暗灰色	RAL 7021	粉末涂层
24630-040	100mm	1200mm	1	暗灰色	RAL 7021	粉末涂层
24630-043	200mm	1200mm	1	暗灰色	RAL 7021	粉末涂层

Table 2/2			
物料号	类型	包装单位	快速发货
24630-083	底座侧板		No
24630-084	底座侧板		No
24630-077	底座侧板	对	No
24630-080	底座侧板	对	No
24630-078	底座侧板	对	No
24630-081	底座侧板	对	No
24630-079	底座侧板	对	No

物料号	类型	包装单位	快速发货
24630-082	底座侧板	对	No
24630-038	底座侧板	对	No
24630-041	底座侧板	对	No
24630-039	底座侧板	对	No
24630-042	底座侧板	对	No
24630-040	底座侧板	对	No
24630-043	底座侧板	对	No

其他产品详情

请单独订购前/后面板的基座/底座。

不能与脚轮结合使用

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations

+1.763.422.2661

Chat with us:

nvent.com/schroff

Europe

Straubenhardt, Germany

+49.7082.794.0

Betschdorf, France

+33.3.88.90.64.90

Warsaw, Poland

+48.22.209.98.35

Assago, Italy

+39.02.932.7141

Chat with us:

nvent.com/schroff

Asia

Shanghai, China

+86.21.2412.6943

Qingdao, China

+86.532.8771.6101

Singapore

+65.6768.5800

Shin-Yokohama, Japan

+81.45.476.0271

Chat with us:

nvent.com/schroff

Middle East & India

Dubai, United Arab

Emirates

+971.4.378.1700

Bangalore, India

+91.80.6715.2001

Istanbul, Turkey

+90.216.250.7374

Chat with us:

nvent.com/schroff



我们强大的品牌组合:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE