

Varistar CP Deco Cabinet With 19" Panel Mounts in Deco Frame



Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

功能

正面开口（无门）

19 寸面板安装件集成在装饰框架中

带单点锁定的后门, 带速卸锁扣的侧板

静态承载能力 400 千克（安装在装饰框架上）

技术参数

产品类型: 机柜
覆层颜色代码: RAL 7021
框架材料: 钢

Table 1/3

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	覆层材料
10630-036	42U	2000mm	暗灰色	600mm	RAL 7021	钢

物料号	机架高度	高度	框架颜色	宽度	框架颜色代码	覆层材料
10630-035	42U	2000mm	暗灰色	600mm	RAL 7021	钢
10630-033	38U	1800mm	暗灰色	600mm	RAL 7021	钢
10630-034	38U	1800mm	暗灰色	600mm	RAL 7021	钢

Table 2/3						
物料号	深度	覆层颜色	包装数量	符合	完成	材料
10630-036	800mm	暗灰色	1	IEC 60297-3-100	粉末涂层	钢
10630-035	600mm	暗灰色	1	IEC 60297-3-100	粉末涂层	钢
10630-033	600mm	暗灰色	1	IEC 60297-3-100	粉末涂层	钢
10630-034	800mm	暗灰色	1	IEC 60297-3-100	粉末涂层	钢

Table 3/3		
物料号	静态负载	快速发货
10630-036	400kg	No
10630-035	400kg	No
10630-033	400kg	No
10630-034	400kg	No

其他产品详情

后门可选配摇柄锁。

ServicePlus EMC 上提供了更多尺寸和版本。请单独订购基座/底座。如装配托盘和滑轨，需要另外订购一对角轨。

警告

应仅根据 nVent 的产品说明书与培训材料安装并使用 nVent 的产品。可访问 www.nvent.com 获取说明书，或者向您的 nVent 客服代表索取。错误安装、使用不当、滥用或未能完全遵守 nVent 的说明与警告，可能会造成产品故障、财产损失、严重的人身伤害及死亡和/或使得保修服务无效。

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



我们强大的品牌组合:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE